




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AF	14		C1	REV PER ECR 05-002915	25MAY05	JR
						KR



- 1 MATERIAL: .032±.001 THK BRASS, 100-86, HEAT TREAT 0.082
- 2 .010 MAX CUT-OFF ALLOWED
- 3 ASSEMBLY SCREW AND TORQUE 2-8 LB-IN
- 4 THREADS DEFORMED SO AS NOT TO ALLOW REMOVAL OF THE SCREW.
- 5 PART TO BE CLEAN AND OIL FREE
- 6 MATERIAL: BINDING HEAD .340 DIA, #10-32 .312 LONG. BRASS SCREW (ELECTRICAL TAPE)
- 7 MATERIAL: BINDING HEAD .340 DIA, #10-32 .312 LONG. BRASS SCREW (ELECTRICAL TAPE) BRIGHT NICKEL FINISH

1	7	-	1	1	T20737542	FASTON TAB ASSEMBLY NICKEL PLATED BRASS SCREW	157727-2
-	-	1	6	1	1	T20737542	FASTON TAB ASSEMBLY BRASS SCREW
SCREW 157423-2	2	SCREW 157423-1	2	FASTON TAB 157728-1	1	EMERSON P/N	DESCRIPTION
							PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 25MAY05	tyco Tyco Electronics Corporation Harrisburg, Pa 17105-3608				
DIMENSIONS: INCHES		CHK K RANDOLPH 26MAY05					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K RANDOLPH 26MAY05					
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± 1° FINISH -		PRODUCT SPEC APPLICATION SPEC WEIGHT -					
MATERIAL -		CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779	DRAWING NO C=157727	RESTRICTED TO -
				SCALE 4:1	SHEET 1 OF 1	REV C1	