

J

I

H

G

F

E

D

C

B

A

J

I

H

G

F

E

D

C

B

A

2176

4

3

2

1

PART NO.

ENG. NO.

DESCRIPTION

05-06-0301

2176-T

TIN PLATE

05-06-0303

2176-AT

WITHOUT DETENT, TIN PLATED

NOT TOOLED

X-2176-999A

WITHOUT DETENT, UNPLATED

05-06-0302




2176-(P90)IL

WITH DETENT, PLATED, LOOSE

05-06-0304

2176-(P90)IAL

WITHOUT DETENT, PLATED, LOOSE



DETENT LOCATION

SCALE 8:1




NOTES:

1. CRIMP FOR #14 THRU #22 GA. WIRE. ALSO (2) #18 GA. WIRE WITH .03(0.79) THK. INSULATION.
2. MATERIAL: .010/(0.25) THK. 70/30 BRASS ALLOY. PRE-TIN PLATED.
3. PRODUCT SPECIFICATION 05-06-1 APPLIES.

SECTION B-B

SECTION A-A

SCALE 8:1



MFG. SH. REV. LTR.

REVISIONS

E

REDRAWN ON CAD
PER UCR2000-0804
00/07/13 ES

TITLE

TERMINAL FOR
.020/(0.51) X .187/(4.75)
SPADE

MOLEX INCORPORATED
LITSE,ILL. 60532 U.S.A.

SHEET NO. 1 OF 1
DATE 92/10/26

SEE CHART

SD-2176-*

DIMENSIONS SHOWN (METRIC) INCH
UNLESS OTHERWISE SPECIFIED
TOLERANCES: ANGULAR ± 1/2°

	INCH	METRIC
3 PLACE	± .010	---
2 PLACE	± .014	± 0.25
1 PLACE	---	± 0.35

DRAFT WHERE APPLICABLE MUST
REMAIN WITHIN DIMENSIONS

DRWG. BY MAB
APP'D. BY RAS

CHK'D. BY KBP
SCALE 8:1

FILE NAME
SD2176X1
DGN

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO
MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIV. CP
SIZE C