

13 12 11 10 9 8 7 6 5 4 3 2 1

J

I

H

G

F

E

D

C

B

A

J

I

H

G

F



E

D

C

B

A



NOTES:

- SEE SHEET 4 & 5 FOR CHARTED DIMENSIONS AND PART NUMBERS.
- FOR FIXED TAIL / PCB PATTERN AT LAST CIRCUIT POSITIONS REFER TO SECTION A-A ON SHEET 2 AND PCB LAYOUTS ON SHEET 3.
- THIS DIMENSION TO MEET SPECIFICATIONS AFTER SHIELD IS FULLY SEATED TO HOUSING AS A RESULT OF A BRACKET OR PANEL.
- REFER TO PS-79058 PRODUCT SPEC. FOR ELECTRICAL, MECHANICAL AND ENVIRONMENTAL SPECIFICATIONS.
- MATERIAL:
RECEPTACLE HOUSING: GLASS FILLED LIQUID CRYSTAL POLYMER;
COLOR-BLACK; UL 94V-0
CONTACTS: PHOSPHOR BRONZE
SHIELD: STEEL WITH BRIGHT NICKEL OVER COPPER
FLASH (OPTIONAL)
GROUNDING CLIP: BRASS WITH TIN OVER NICKEL PLATE
- PACKAGING:
PARTS PACKAGED IN TUBES PER PK-70873-0207

TERMINAL FINISH:

SELECTIVE GOLD: THICKNESS= 30 MICROINCHES/(0.76 MICROMETERS) MINIMUM.
SELECTIVE TIN: THICKNESS= 75 MICROINCHES/(1.90 MICROMETERS) MINIMUM.
NICKEL UNDERPLATE OVERALL.

NOTE FOR LEAD FREE CONVERSION:

THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO ROHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC". CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH LEAD.

REV	DESCRIPTION	DATE	BY
1	UPDATE REV LEVEL	2005/03/11	DRW:WJW
2	EC NO: UCP2005-1072	2005/03/11	CHKD:WJW
3	APPR:SMILLER	2005/03/28	APPR:SMILLER

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)
▽=0	mm INCH
▽=0	4 PLACES ± --- ± ---
▽=0	3 PLACES ± --- ± .005
▽=0	2 PLACES ± 0.13 ± ---
▽=0	1 PLACE ± --- ± ---
▽=0	ANGULAR ±1/2°
▽=0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE	SCALE	DESIGN UNITS
IN/MM	4:1	INCH
DRAWN BY	DATE	TITLE
JLONG	03/27/1989	SCSI SHIELDED RECEPTACLE ASSEMBLY WITH LATCHES
CHECKED BY	DATE	
BOWEN	03/27/1989	
APPROVED BY	DATE	
DJB	03/27/1989	
MATERIAL NO.	DOCUMENT NO.	SHEET NO.
SEE TABLE	SDA-79059-2***	1 OF 5

5	S
4	S
3	S
2	S
1	S
SHT, REV.	

12 11 10 9 8 7 6 5 4 3 2 1

13

12

11

10

9

8

7

6

5

4

3

2

1

J

I

H

G

F

E


D

C

B

A


.063
(1.60)
REF.



SECTION A-A

68 CIRCUIT TYPE II TAIL VERSION
50 CIRCUIT

.063
(1.60)
REF.




SECTION A-A

68 CIRCUIT TYPE I TAIL VERSION ONLY

$\Phi .006 / (.015) \text{ M } Z X Y$

.024 $\pm$.002
(0,61 $\pm$ 0,05)




$\Phi .006 / (.015) \text{ M } Z Y X$

.034 $\pm$.003
(0,86 $\pm$ 0,08)

PIN WINDOW DETAIL

SCALE 10:1



SECTION B-B

CHG TYPE I & II DESC EC NO: UCP2005-1072 5 DRAWN BY: DRWNSMART CHKD: HBARKER APPR: SMILLER REV	QUALITY SYMBOLS DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 8:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	TITLE SALES ASSEMBLY SCSI SHIELDED RECEPTACLE WITH LATCHES MOLEX INCORPORATED	SHEET NO. 2
		 =0  =0	mm INCH	DRAWN BY DATE JLONG 04/14/1989	CHECKED BY DATE BOWEN 04/14/1989	APPROVED BY DATE DJB 04/14/1989	DOCUMENT NO. SDA-79059-2***			
		4 PLACES ± --- ± ---								
		3 PLACES ± --- ± .005								
		2 PLACES ± 0.13 ± ---								
		1 PLACE ± --- ± ---								
		ANGULAR ± 1/2°		SEE TABLE						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

12

11

10

9

8

7

6


5

4

3

2

1



[illegible]