


1. Do not use any part other than that specified in this drawing.
2. All dimensions are in inches unless otherwise noted.
3. All dimensions are to be held to 1500 unless otherwise noted.
4. Proper Crimp-Adjustment



INSULATION CRIMP .224
.238


.310
.333 GASKET CRIMP

BRAID CRIMP .211
.221


FERRULE

PLUG ASSY
#2-330953-3

METHOD OF GAGING CRIMP DIMS
THE CRIMP DIMS APPLY ONLY
TO THE ABOVE COMBINATIONS
ON A CRIMPED PRODUCT.



CENTER CONTACT
CRIMP
SECTION A-A



SUPERSEDED BY LS 2349

2	24058-6	CURVED WASHER	10
1	307089-2	LOCATOR	9
2	125115-1	WASHER	8
4	21045-6	RING - RETAINING	7
1	300449	PIN - RETAINING	6
1	39364	SPRING	5
1	39366	COLLAR	4
2	58123	PIN - RETAINING	3
2	1-306055-3	PIN - RETAINING	2
6	21045-3	RING - RETAINING	1

2	DWG SIZE	NUMBER	NAME	REMARKS	REV NO
©1967 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.					
DR Cf. Flaymick 3-16-67		MATERIAL AND FINISH ---		CUSTOMER COPY REFERENCE ONLY	
CHK Rf. J. J. J. 3-29-67		WIRE - RANGE - INSULATION RG-55B		AMP INCORPORATED HARRISBURG, PENNA.	
DE ---		TOLERANCE EXCEPT AS NOTED ± .015 ± .001		CLASS ---	
APP E. J. J. 4-10-67		SCALE 1-1		TYPE BNC-TNC	
		NAME ---		LOC M/B	
				NO 69376-2	
				ET	
HAND TOOL ASSEMBLY					

69376-2	REVISION RECORD	DR	CHK	DATE
E1	SUP BY I.S. 2349	ENR	ENR	3-30-67
E	REVISED	PL	PL	3-1-71
D	REVISED	BS	BS	1-1-71
C	REVISED	PL	PL	1-25-67
B	REVISED	PL	PL	2-3-67
A	REVISED	BS	BS	8-9-67

PRINTED 12/67
DIMENSIONS IN INCHES
DO NOT SCALE PRINT
E-1
18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[69376-2](#)