


Vishay General Semiconductor


Schottky Barrier Plastic Rectifier



PRIMARY CHARACTERISTICS					
I _{F(AV)}	1.0 A				
V_{RRM}	20 V, 30 V, 40 V				
I _{FSM}	25 A				
V _F	0.45 V, 0.55 V, 0.60 V				
T _J max.	125 °C				
Package	DO-204AL				
Diode variations	Single				

FEATURES





· Extremely fast switching

Low forward voltage drop

• High frequency operation

riigir ir equeriey operation

Solder dip 275 °C max. 10 s, per JESD 22-B106

 Material categorization: For definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, freewheeling, DC/DC converters, and polarity protection applications.

MECHANICAL DATA

Case: DO-204AL (DO-41)

Molding compound meets UL 94 V-0 flammability rating

Base P/N-E3 - RoHS-compliant, commercial grade

Terminals: Matte tin plated leads, solderable per

J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test **Polarity:** Color band denotes the cathode end

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)						
PARAMETER	SYMBOL	1N5817	1N5818	1N5819	UNIT	
Maximum repetitive peak reverse voltage	V _{RRM}	20	30	40	V	
Maximum RMS voltage	V _{RMS}	14	21	28	V	
Maximum DC blocking voltage	V _{DC}	20	30	40	V	
Maximum non-repetitive peak reverse voltage	V _{RSM}	24	36	48	V	
Maximum average forward rectified current at 0.375" (9.5 mm) lead length at T _L = 90 °C	I _{F(AV)}	1.0			А	
Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	25			А	
Voltage rate of change (rated V _R)	dV/dt	10 000			V/µs	
Operating junction and storage temperature range	T _J , T _{STG}	- 65 to + 125			°C	

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)						
PARAMETER	TEST CONDITIONS	SYMBOL	1N5817	1N5818	1N5819	UNIT
Maximum instantaneous forward voltage	1.0	V _F ⁽¹⁾	0.450	0.550	0.600	V
Maximum instantaneous forward voltage	3.1	V _F ⁽¹⁾	0.750	0.875	0.900	V
Maximum average reverse current	T _A = 25 °C	I _B ⁽¹⁾		mA		
at rated DC blocking voltage	T _A = 100 °C	I 'R ''	10			IIIA
Typical junction capacitance	4.0 V, 1.0 MHz	CJ	125	1	10	pF

Note

⁽¹⁾ Pulse test: 300 μs pulse width, 1 % duty cycle



Vishay General Semiconductor

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	OL 1N5817 1N5818 1N5819		UNIT	
Typical thermal resistance	R _{0JA} (1)	50			°C/W
	R _{0JL} (1)	15			

Note

⁽¹⁾ Thermal resistance from junction to lead vertical PCB mounted, 0.375" (9.5 mm) lead length with 1.5" x 1.5" (38 mm x 38 mm) copper pads

ORDERING INFORMATION (Example)					
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE	
1N5819-E3/54	0.332	54	5500	13" diameter paper tape and reel	
1N5819-E3/73	0.332	73	3000	Ammo pack packaging	

RATINGS AND CHARACTERISTICS CURVES

(T_A = 25 °C unless otherwise noted)




Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 4 - Typical Reverse Characteristics



Vishay General Semiconductor




Fig. 5 - Typical Junction Capacitance





Fig. 6 - Typical Junction Capacitance

100 (OV) 100

Fig. 7 - Typical Transient Thermal Impedance

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.