

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY - ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD


A

RELEASED







21JUL2014

J. J


W. H



3D VIEW
ONLY FOR REFERENCE



OUTLINE OF
KEEP OUT AREA



RECOMMENDED MATING PWB LAYOUT

SPRING FINGER POSITION

- 1 PART NUMBER: SEE TABLE.
- 2 MATERIAL: SUS THICKNESS=0.10MM.
- 3 PLATING: 2um MIN. NICKEL UNDERLAYER ALL OVER
0,50um MIN. GOLD ON CONTACT SURFACE
GOLD FLASH ON SOLDERING SURFACE
- 4 PICK AND PLACE SURFACE Ø1.2MM.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 23SEP2013

CHK Tony Zhang

APVD Wenke He 23SEP2013

Wenke He

PRODUCT SPEC

108-115061-1

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

SPRING FINGER
TYPE A

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-2199248

SCALE 25:1 SHEET 1 OF 2 REV A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY - ALL RIGHTS RESERVED.

LOC
ES

DIST
00

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

DIM A+0.05 ±0.10

4,00±0,10

2,00±0,10

Ø1.50^{+0.10}₋₀

4,00±0,10

1,75±0,10

4,10
REF

5,50±0,10

12,00±0,30

0,35±0,05

4,00

2,08±0,10

1,58±0,10

SECTION Z-Z

FRANGE CORE DIA
Ø100±1

Ø330±1
REEL DIA.

12.4⁺²₀

18.4 MAX
REEL WIDTH

300mm REF
WITHOUT CHARGE

WEEDING THE COVER TAPE.
1000mm REF

165,000°~180°
PEELING ANGLE
0.1~1.3N(300mm/min)
PEELING STRENGTH

WITH PRODUCT CHARGE
(QUANTITY) EA/IREEL
SEE TABLE ON SHEET 1

WITHOUT CHARGE
100~125HOLES

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN -

CHK -

APVD -

PRODUCT SPEC

108-115061-1

APPLICATION SPEC

-

WEIGHT -

CUSTOMER DRAWING

TE

TE Connectivity

NAME

SPRING FINGER
TYPE A

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-2199248 -

SCALE 5:1 SHEET 2 OF 2 REV A