




DIMENSIONS mm (inches)



PART NUMBER		8609		71		7		5	
row a	PIN OUT	1	32	2	64	3	96	4	64
rows a-b									
rows a-b-c									
rows a-c									
NUMBER OF CONTACTS		13							
TERMINATION		L = 2.75 ±0.15 (.108) A = Ø0.6 0 -0.08 B = Ø0.8 0 +0.3 13							
PERFORMANCE CLASS		DIN 41612 class 3 4							
DIN 41612 class 2									
DIN 41612 class 1									
TERMINATION TYPE		TIN LEAD 251E1							
LEAD FREE		ANLF							

PCB DRILLING



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C-8609-0000A

European Views

www.fciconnect.com		surface ISO 1302		tolerance std ISO 406 ISO 1101		projection mm	
TOLERANCES UNLESS OTHERWISE SPECIFIED		ANGULAR		LINEAR		size A3	
Dr ROUILLARD 2000/11/20		0.X		±0.1		Scale 1.5	
Eng TARON 2000/11/20		0.XX		±0.1		ECN LS08-0094	
Chr LEGARE 2000/11/20		0.XXX		±0.1		Spec ref -	
Appr LEGARE 2000/11/20		Product family		DIN 8609		Dwg no C-8609-0850	
FCI		title RIGHT ANGLE MALE - STYLE C		catalog no SEE TABLE		Rev. D	
		SOLDER TO BOARD		CUSTOMER		sheet 1 of 1	

SPECIFICATION 251 = specific marking : only date code
or SPECIFICATION AN=

rev	ecn no	dr	date
A	-	-	2000/11/20
B	LS05-001	JTA	2005/03/03
C	LS06-0095	LGO	2006/06/26
D	LS08-0094	HLE	2008/04/04
-	-	-	-
-	-	-	-
-	-	-	-