





DAUGHTERCARD HOLE PATTERN (CONNECTOR SIDE)

NOTES:

1. MATERIALS: HOUSING - LIQUID CRYSTAL POLYMER (LCP)GLASS-FILLED, UL 94V-0
TERMINALS - HIGH PERFORMANCE COPPER ALLOY
2. FINISH: SELECTIVE GOLD (Au) IN CONTACT AREA,
SELECTIVE MATTE TIN (Sn) IN TAIL AREA,
NICKEL (Ni) UNDERPLATE OVERALL.
3. REFER TO MOLEX PRODUCT SPECIFICATION PS-75710-999 FOR PERFORMANCE SPECS.
4. PRODUCT IS PACKAGED PER PK-70873-607.
5. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPEC PS-45499-002.
6. GUIDED PARTS TO BE SHIPPED WITH 2-32 TYPE AB
SELF-TAPPING SCREW P/N 73726-0005.
7. FOR GROUNDED GUIDE MODULES USE DIA 2.45+/-0.10 (PTH), DIA 2.58 (DRILL),
AND DIA 4.50 (PAD).
8. MAPS (MOLEX ADVANCED PLATING SYSTEM).

LEAD FREE CON/MAPS EC NO: UCP2013-4120 DRWN:BBARKER 2012/11/12 CHKD:MMOLFE 2013/03/19 APPR:SMILLER 2013/08/05	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY MCARRANZA	DATE 3/20/06	TITLE I-TRAC DAUGHTERCARD 7 ROW GUIDE RIGHT SIGNAL MODULE				
			4 PLACES ±---	±---	CHECKED BY JLAURX	DATE 3/21/06	molex					
			3 PLACES ±---	±---	APPROVED BY JLAURX	DATE 3/21/06						
			2 PLACES ±0.13	±---	ANGULAR ±1/2°			DOCUMENT NO. SD-76020-004				
			1 PLACE ±0.25	±---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					SHEET NO. 1 OF 2		
			0 PLACE ±	±	SEE CHART							
			SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

MATERIAL NUMBER	# OF COLUMNS	DIM. "A" MAX.	DIM. "B"
76020-***4	4	22.20	11.10
76020-***6	6	29.60	18.50
76020-***0	10	44.40	33.30

76020-****

MODULE STYLE AND TAIL PLATING TYPE
4 = GUIDE RIGHT, MATTE TIN (FORMERLY TIN/LEAD)
5 = GUIDE RIGHT, MATTE TIN

POLARIZATION KEY ORIENTATION
0 = NO KEY
1 = A
2 = B
3 = C
4 = D
5 = E
6 = F
7 = G
8 = H

OF COLUMNS/PLATING
04 = 4 COL 30 GOLD
06 = 6 COL 30 GOLD
10 = 10 COL 30 GOLD
44 = 4 COL 10 GOLD (MAPS)
46 = 6 COL 10 GOLD (MAPS)
40 = 10 COL 10 GOLD (MAPS)
54 = 4 COL W/ESD CLIP 30 GOLD
56 = 6 COL W/ESD CLIP 30 GOLD
50 = 10 COL W/ESD CLIP 30 GOLD
74 = 4 COL W/ESD CLIP 10 GOLD (MAPS)
76 = 6 COL W/ESD CLIP 10 GOLD (MAPS)
70 = 10 COL W/ESD CLIP 10 GOLD (MAPS)

SEE SHEET 1 EC NO: UCP2013-4120 2012/11/12 DRWN:BBARKER CHKD:MMOLFE 2013/03/19 APPR:SMILLER 2013/08/05	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY MCARRANZA	DATE 3/20/06	TITLE I-TRAC DAUGHTERCARD 7 ROW GUIDE RIGHT SIGNAL MODULE molex	DOCUMENT NO. SD-76020-004	SHEET NO. 2 OF 2	
			4 PLACES	± ---	± ---	CHECKED BY JLAURX	DATE 3/21/06				
			3 PLACES	± ---	± ---	APPROVED BY JLAURX	DATE 3/21/06				
			2 PLACES	± 0.13	± ---	MATERIAL NO.					
			1 PLACE	± 0.25	± ---	SEE CHART					
			0 PLACE	±	±	SIZE 		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
			ANGULAR ±1/2°			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					