




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING


Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



MOUNTING HARDWARE



LOCK WASHER



HEX NUT

NOTES:

1. OPERATING TEMPERATURE RANGE: -55°C TO +125°C.
2. SILVER PLATED CASE, LEAD AND MOUNTING HARDWARE.
3. MAX. RECOMMENDED MOUNTING TORQUE : 2.0 lb. - in.
4. MAX. RECOMMENDED SOLDERING TEMPERATURE : 260°C.
SEE INSTALLATION RECOMMENDATIONS.
5. LOCKWASHER AND HEX NUT INCLUDED.
6. TUSONIX TRADEMARK AND PART VARIATION NUMBER
STAMPED ON HEX FLATS.
7. FLASH AT 500 VDC FOR 25 SECONDS

STYLE	VAR.	CAP. (pF)	TOLERANCE	125° WORKING VOLTAGE		CURRENT D.C. (AMPS)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220				
				85° C	125° C		1MHz	10MHz	100MHz	1GHz	10 GHz
4400	074	10,000	GMV	---	115VAC 200VDC	10A	4	21	35	50	60

X-2015 Rev-0	REVISION RECORD	Original Release C.O. 19980623-2-01	0		--TOLERANCES-- Unless Otherwise Specified		Title			
					DECIMAL ± 		BUSHING STYLE EMI FILTER			
					ANGLES ± 					
					TUSONIX TUCSON, ARIZONA		Drawn		S.M. 06-26-98	Scale 5X
							Approved			S.C. 06-26-98
		A		4400-074						