


Darlington Transistors



Features:

- Designed for general-purpose amplifier and low speed switching applications
- Collector-emitter sustaining voltage - $V_{CEO(sus)} = 60\text{ V}$ (minimum) - TIP120, TIP125
80 V (minimum) - TIP121, TIP126
100 V (minimum) - TIP122, TIP127
- Collector-emitter saturation voltage - $V_{CE(sat)} = 2\text{ V}$ (maximum) at $I_C = 3\text{ A}$
- Monolithic construction with built-in base-emitter shunt resistors



- Pin 1.** Base
2. Collector
3. Emitter
4. Collector (Case)


Dimensions	Minimum	Maximum
A	14.68	15.31
B	9.78	10.42
C	5.01	6.52
D	13.06	14.62
E	3.57	4.07
F	2.42	3.66
G	1.12	1.36
H	0.72	0.96
I	4.22	4.98
J	1.14	1.38
K	2.2	2.97
L	0.33	0.55
M	2.48	2.98
O	3.7	3.9

Dimensions : Millimetres

NPN
TIP120
TIP121
TIP122

PNP
TIP 125
TIP 126
TIP 127

5 A
Darlington
Complementary Silicon
Power Transistors
60 to 400 V
65 W



TO-220

Maximum Ratings

Parameter	Symbol	TIP120	TIP121	TIP122	Unit
		TIP125	TIP126	TIP127	
Collector-Emitter Voltage	V _{CEO}	60	80	100	V
Collector-Base Voltage	V _{CBO}				
Emitter-Base Voltage	V _{EBO}	5			
Collector Current - Continuous - Peak	I _C I _{CM}	5 8			A
Base Current	I _B	120			mA
Total Power Dissipation at T _C = 25°C Derate above 25°C	P _D	65 0.52			W W / °C
Operating and Storage Junction Temperature Range	T _J , T _{STG}	-65 to +150			°C


Darlington Transistors



Thermal Characteristics

Characteristic	Symbol	Maximum	Unit
Thermal Resistance Junction to Case	$R_{\theta jc}$	1.92	$^{\circ}\text{C} / \text{W}$

Power Derating



Electrical Characteristics ($T_C = 25^{\circ}\text{C}$ unless otherwise noted)

Characteristic		Symbol	Minimum	Maximum	Unit
Off Characteristics					
Collector-Emitter Breakdown Voltage (1) (I _C = 30 mA, I _B = 0)	TIP120, TIP125 TIP121, TIP126 TIP122, TIP127	V _{CEO} (SUS)	60 80 100	-	V
Collector Cut off Current (V _{CE} = 30 V, I _B = 0) (V _{CE} = 40 V, I _B = 0) (V _{CE} = 50 V, I _B = 0)	TIP120, TIP125 TIP121, TIP126 TIP122, TIP127	I _{CEO}	-	0.5 0.5 0.5	mA
Collector Cut off Current (V _{CE} = 60 V, I _B = 0) (V _{CE} = 80 V, I _B = 0) (V _{CE} = 100 V, I _B = 0)	TIP120, TIP125 TIP121, TIP126 TIP122, TIP127	I _{CBO}	-	0.2 0.2 0.2	
Collector Cut off Current (V _{EB} = 5 V, I _C = 0)		I _{EBO}	-	2	
On Characteristics (1)					
DC Current Gain (I _C = 0.5 A, V _{CE} = 3 V) (I _C = 3 A, V _{CE} = 3 V)		h _{FE}	1,000 1,000	-	-
Collector-Emitter Saturation Voltage (I _C = 3 A, I _B = 12 mA) (I _C = 5 A, I _B = 20 mA)		V _{CE} (sat)	-	2 4	V
Base-Emitter on Voltage (I _C = 3 A, V _{CE} = 3 V)		V _{BE} (on)	-	2.5	

Darlington Transistors




Dynamic Characteristics				
Small-Signal Current Gain ($I_C = 3\text{ A}$, $V_{CE} = 4\text{ V}$, $f = 1\text{ MHz}$)	h_{fe}	4	-	-
Output Capacitance ($V_{CB} = 10\text{ V}$, $I_E = 0$, $f = 0.1\text{ MHz}$)	C_{ob}	-	300 250	pF
TIP120, TIP121, TIP122 TIP125, TIP126, TIP127				

(1) Pulse Test : Pulse width = 300 μ s, duty cycle $\leq$ 2%

Internal Schematic Diagram

NPN
TIP120
TIP121
TIP122



PNP
TIP125
TIP126
TIP127




Figure - 2 Switching Time




Figure - 4 Small Signal Current Gain




Figure - 3 Switching Time




Figure - 5 Capacitances





Figure - 6 Active Region Safe Operating Area



There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown safe operating area curves indicate $I_C - V_{CE}$ limits of the transistor that must not be subjected to greater dissipation than the curves indicate. The data of Figure - 6 is based on $T_{J(PK)} = 150^\circ\text{C}$; T_C is variable depending on power level. Second breakdown pulse limits are valid for duty cycles to 10% provided $T_{J(PK)} \leq 150^\circ\text{C}$. At high case temperatures, thermal limitation will reduce the power that can be handled to values less than the limitations imposed by second breakdown.

Figure - 7 DC Current Gain





Figure - 8 Collector Saturation Region







Figure - 9 "ON" Voltage



Specification Table

I _C A	V _{CEO} (Maximum) V	h _{FE} Minimum at I _C = 3A	P _{tot} at 25°C W	Package	Part Number	
					NPN	PNP
5	60	1,000	65	TO-220	TIP120	TIP125
	80				TIP121	TIP126
	100				TIP122	TIP127

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.