

## **TLS 2200 Thermal Labeling System w/AC Power & Quick Charger**

### **TLS-AC-QC**

<b>Agency Approval(s)/Compliance:</b>	FCC Class A approved
<b>Print Resolution:</b>	203 dpi
<b>Print Technology:</b>	Thermal Transfer
<b>Application(s):</b>	Circuit Board Labeling, Data Communications Labeling, Facility, Safety & Maintenance Identification, General & Industrial Labeling, Healthcare Identification, Laboratory Identification, Panel Identification, Security Identification, Wire & Cable Marking
<b>Keyboard:</b>	ABC
<b>Max Labels Per Day:</b>	750 labels/day
<b>Display:</b>	LCD
<b>Character Height:</b>	4 to 72 pt.
<b>Max Label Width:</b>	2.000"
<b>Max Print Width:</b>	1.81"
<b>Max Print Length:</b>	Up to 54" (1371.60mm)
<b>Max Roll Length:</b>	50' (500' bulk)
<b>Text Sizes:</b>	1 to 19 (4 to 72 point)
<b>Color Capability:</b>	Single Color Printing
<b>Multi-Line Print:</b>	Yes
<b>Print Rotation:</b>	Yes
<b>Serialization:</b>	Yes
<b>Bar Code Type:</b>	1D (Linear)

<b>PC Connectivity:</b>	Yes
<b>Peripheral Printing:</b>	Yes
<b>Stand Alone Printing:</b>	Yes
<b>Connectivity Options:</b>	Serial
<b>Portability:</b>	Yes
<b>Memory:</b>	21,000 characters, 10 label lists
<b>Power Supply:</b>	Rechargeable Battery, AC Power (optional)
<b>Operating Temperature:</b>	40° - 120°F (4° - 49°C)
<b>Materials Supported:</b>	Continuous/Die Cut, Bulk, Over 500 stock parts/custom
<b>Continuous vs Die Cut Labels:</b>	Can print both continuous and die cut labels.
<b>Dimensions:</b>	11.500in x 4.250in x 4.000 in (292.10mm x 107.95mm x 101.60mm)
<b>Weight:</b>	2.75lb (1.25kg)
<b>Warranty:</b>	12 Months - See Terms and Conditions