



FIT 25mm HEAT SHRINK SLEEVE AT EACH END

PART NUMBER	CONNECTOR A	CONNECTOR B	LENGTH L
078161-0601	STRAIGHT SMA	STRAIGHT SMA	304mm (12")
078161-0602	STRAIGHT SMA	STRAIGHT SMA	457mm (18")
078161-0603	R/A SMA	STRAIGHT SMA	304mm (12")
078161-0604	R/A SMA	STRAIGHT SMA	457mm (18")

NOTE
078161-0603 SHOWN
AS EXAMPLE

WARNING
This Copy will not be
kept up-to-date.

1	PROD RELEASE DCN K5968	5-Jul-05
B	WAS RD031205-601-4	27-Jun-05
A	PROVISIONAL	02-Sep-04
Iss Rev	DCN/ECN or Description	Date

DO NOT SCALE			PDM: ...	Total Surface Area : mm ²	Total Volume : 0.000 mm ³	Generic Model:
Drawn	PJ	02-Sep-04	Material:	 3rd ANGLE PROJECTION Surface Roughness	Jays Close, Viables Estate, Basingstoke, Hants. RG22 4BA, UK	Title BENCH TEST CABLE MINI RF SERIES
Checked	AI	05-Jul-05				
Engineer.	PJ	.				
Manufact.	.	.				
Assembly	.	.	Treatment:	63.0	Ref:	Drwg. No. 76228Y
Quality	.	.		Unless Specified	Cust Spec No:	
Approvals	Sign	Date		Dimensions in: mm	A4/Letter	
This is issued in strict confidence on condition that it is not used as a basis for manufacture or sale and that it is not copied, reprinted or disclosed to a third party either wholly or in part without the prior written consent of ITT Industries © 02-Sep-04						