







SECTION Y-Y

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADERS			
litr	ecn no	dr	date	tolerances unless otherwise specified						title			
A	V71646	SAR	12/15/97	angles	linear.	.XX±.01/.3		INCH/MM		HEADER, SLIM-LINE VERTICAL ASS'Y, 2-WALL			
B	V81270	SAR	8/5/98			.XXX±.005/.13							
C	V94352	DAI	11/17/99			.XXXX±.0020/.051							
D	M05-0089	ERE	5/20/05	dr	S. ROYER	12/15/97			dwg no		sheet 1 of 2 size 74374 A3		
E	M07-0116	AGS	2/25/07	engr	L. FYE	12/15/97							
				chr	L. FYE	12/15/97							
				appd	L. FYE	12/15/97			type		Product Customer Drawing		
sheet index		revision sheet		E	E								
		1 2											

PRODUCT NO.

74374 - F ZZ Y LF

F	PLATING NOTE 10
1	30μ / 0.76μm GOLD
5	30μ / 0.76μm GXT

NO. OF PINS ZZ	POSITIONS	DIM B	DIM C
10	2 X 5	.630/16.00	.400/10.16
14	2 X 7	.830/21.80	.600/15.24
26	2 X 13	1.430/35.60	1.200/30.48
34	2 X 17	1.830/46.48	1.600/40.64
40	2 X 20	2.130/54.10	1.900/48.26

Y	DIM D TAIL LENGTH
2	.120/3.05

LEAD FREE OPTION
NOTE 7

NOTES:

- ① PLASTIC MATERIAL: 30% GLASS FILLED, BLACK PCT
FLAME RETARDANT PER UL-94-V0
- ② PIN MATERIAL: PHOS BRONZE.
3. 4 LBS/1.8 KG MIN PIN RETENTION.
- ④ PIN CONTACT SURFACE IS TO BE FREE OF BURRS,
SCRATCHES AND PLASTIC DEBRIS.
5. PACKAGING: ADD 'T' TO THE END OF THE 4-DIGIT DASH NO.
TUBE PACKAGING. [ex 74374-1402T]
6. PART NUMBERS WITH "R" FOLLIWING THE DASH NUMBER
WILL HAVE RETENTIVE TAILS. [ex 74374-1402TR]
TWO PAIR OF PINS LOCATED APPROXIMATELY IN THE CENTER
OF 2X14 AND SMALLER SIZE ARE TO BE KINKED.
TWO PAIR OF PINS LOCATED ON EACH END OF 2X15 AND LARGER
ARE TO HAVE 2 PAIR OF PINS KINKED ON EACH END.
- ⑦ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
8. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.
- ⑨ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- ⑩ PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family HEADERS
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM scale 1:1	title
E				angles	.XX±.01/.3		HEADER, SLIM-LINE VERTICAL ASS'Y, 2-WALL
				linear	.XXX±.005/.13		
				0°±2°	.xxxx±.0020/.051		
		dr	S. ROYER	12/15/97			dwg no
		enrg	L. FYE	12/15/97			sheet2 of 2
		chr	L. FYE	12/15/97			size
		appd	L. FYE	12/15/97			A3
sheet	revision						type Product Customer Drawing
index	sheet						

form: A3