




D


C

B



A



- 1. WIRE RANGE: 0.3 - 0.05 MM² (30 - 22 AWG)
- 2. INSULATION RANGE: 1.91 MAX



RECOMMENDED CUT OUT
FOR 1.57 MAX THICK PANEL



SECTION A-A

SECTION B-B

1.32	.052	1.96	.077	5.08	.200	-	-
1.17	.046	1.91	.075	3.89	.153	-	-
0.76	.030	1.88	.074	3.05	.120	-	-
0.58	.023	1.78	.070	2.67	.105	-	-
0.25	.010	1.65	.065	2.51	.099	13.89	.547
0.13	.005	1.60	.063	2.31	.091	13.64	.537
0.05	.002	1.57	.062	2.29	.090	12.24	.482
0.00	.000	1.40	.055	2.11	.083	5.72	.225
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
2.51 PH BRZ

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±-

FINISH
MATTE TIN

DWN T. BECK 3-10-97
CHK R. SWING 3-10-97
APVD A. BEDDICK 5-16-97

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

CUSTOMER DRAWING

AMP Incorporated
Harrisburg, PA 17105-3608

TERMINAL, 30-22 AWG, .075 MAX INSULATION, AMP-EDGE™

SIZE A2 CAGE CODE 00779 DRAWING NO. 61455 RESTRICTED TO -

SCALE 10:1 SHEET 1 OF 1 REV G