

TOSHIBA PHOTOCOUPLER GaAlAs IRED & PHOTO-IC

TLP117

PDP (Plasma Display Panel)


FA (Factory Automation)

High-Speed Interface

The Toshiba TLP117 consists of a GaAlAs infrared light-emitting diode and an integrated high-gain, high-speed photodetector.

- Inverter logic (totem-pole output)
- Package type : MFSOP6
- Guaranteed performance over temperature : -40 to 105°C
- Power supply voltage : 4.5 to 5.5 V
- Input thresholds current : $I_{FHL} = 5$ mA (max)
- Propagation delay time (tpHL/tpLH) : 30 ns (max) at $V_L = 0$ V
: 20 ns (max) at $V_L = 1.1$ V
- Switching speed : 50 MBd (typ.)
- Common mode transient immunity : 10 kV/μs (min)
- Isolation voltage : 3750 Vrms
- UL Recognized : UL1577, File No.E67349
- c-UL Recognized: CSA Component Acceptance Service No. 5A, File No.E67349
- Option (V4) VDE approved : DIN EN60747-5-5(Note 1)



(Note 1) : When a EN60747-5-5 approved type is needed, please designate "Option(V4)"



Weight: 0.09 g (typ.)

Truth Table

Input	LED	M1	M2	Output
H	ON	OFF	ON	L
L	OFF	ON	OFF	H

Pin Configuration (Top View)**Schematic**

0.1μF bypass capacitor must be connected between pins 6 and 4

Start of commercial production
2007-05

Absolute Maximum Ratings (Ta=25°C)

Characteristic		Symbol	Rating	Unit
LED	Forward current	I _F	25	mA
	Forward current derating (Ta≥85°C)	ΔI _F /ΔTa	-0.7	mA/°C
	Peak transient forward current (Note 1)	I _{FPT}	1	A
	Reverse voltage	V _R	6	V
	Diode power dissipation	P _D	40	mW
	Diode power dissipation derating (Ta≥85°C)	ΔP _D /ΔTa	-1.0	mW/°C
DETECTOR	Output current	I _O	10	mA
	Output voltage	V _O	6	V
	Supply voltage	V _{CC}	6	V
	Output power dissipation	P _O	40	mW
Operating temperature range		T _{opr}	-40 to 105	°C
Storage temperature range		T _{stg}	-55 to 125	°C
Lead solder temperature(10s)		T _{sol}	260	°C
Isolation voltage (AC,60 s, R.H. ≤ 60%,) (Note 2)		BVs	3750	Vrms

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc.).

Note 1: Pulse width PW≤1μs, 300 pps.

Note 2: This device is regarded as a two-terminal device: pins 1 and 3 are shorted together, and pins 4,5 and 6 are shorted together.

Recommended Operating Conditions

Characteristic	Symbol	Min	Typ.	Max	Unit
Input current , ON	I _{F(ON)}	10	—	16	mA
Input voltage , OFF	V _{F(OFF)}	0	—	1.0	V
Supply voltage(*) (Note 1)	V _{CC}	4.5	5.0	5.5	V

* This item denotes operating ranges, not meaning of recommended operating conditions.

Note: Recommended operating conditions are given as a design guideline to obtain expected performance of the device. Additionally, each item is an independent guideline respectively. In developing designs using this product, please confirm specified characteristics shown in this document.

Note 1: The detector of this product requires a power supply voltage (V_{CC}) of 4.5 V or higher for stable operation. If V_{CC} is lower than this value, I_{CC} may increase or the output may be unstable.

Be sure to use the product after checking the supply current, and the operation of a power-on/-off.

Electrical Characteristics

(Unless otherwise specified, $T_a = -40$ to $105^\circ C$, $V_{CC} = 4.5$ to $5.5V$)

Characteristic	Symbol	Test Circuit	Conditions	Min	Typ.	Max	Unit	
Input forward voltage	V_F	—	$I_F = 10 \text{ mA}$, $T_a = 25^\circ C$	1.45	1.6	1.85	V	
Temperature coefficient of forward voltage	$\Delta V_F / \Delta T_a$	—	$I_F = 10 \text{ mA}$	—	-2.0	—	$\text{mV}/^\circ C$	
Input reverse current	I_R	—	$V_R = 5 \text{ V}$, $T_a = 25^\circ C$	—	—	10	μA	
Capacitance between Input terminals	C_T	—	$V_F = 0 \text{ V}$, $f = 1 \text{ MHz}$, $T_a = 25^\circ C$	—	60	—	pF	
Output voltage	“L” Level	V_{OL}	1	$I_{OL} = 4 \text{ mA}$, $I_F = 10 \text{ mA}$	—	—	0.6 V	
	“H” Level	V_{OH}	2	$I_{OH} = -4 \text{ mA}$, $V_{CC} = 4.5 \text{ V}$ $V_F = 1.05 \text{ V}$ $V_{CC} = 5.5 \text{ V}$	3.9 4.9	— —	— —	V
Supply current	“L” Level	I_{CCL}	3	$I_F = 10 \text{ mA}$	—	—	5.0 mA	
	“H” Level	I_{CCH}	4	$V_F = 0 \text{ V}$	—	—	5.0 mA	
Input current	Output : $H \rightarrow L$	I_{FHL}	—	$I_O = 20 \mu\text{A}$, $V_O < 0.3 \text{ V}$	—	—	5 mA	
Input voltage	Output : $L \rightarrow H$	V_{FLH}	—	$I_O = -20 \mu\text{A}$, $V_O > 4.0 \text{ V}$	0.8	—	—	V

*All typical values are at $T_a = 25^\circ C$ unless otherwise specified.Isolation Characteristics ($T_a = 25^\circ C$)

Characteristic	Symbol	Test Conditions	Min	Typ.	Max	Unit
Capacitance input to output	C_S	$V_S = 0 \text{ V}$, $f = 1 \text{ MHz}$	—	0.8	—	pF
Isolation resistance	R_S	$R.H. \leq 60\%$, $V_S = 500 \text{ V}$	1×10^{12}	10^{14}	—	Ω
Isolation voltage	BVs	AC, 60 s	3750	—	—	V_{rms}
		AC, 1 s, in oil	—	10000	—	
		DC, 60 s, in oil	—	10000	—	Vdc

Note : A ceramic capacitor ($0.1 \mu\text{F}$) should be connected from pin 6 to pin 4 to stabilize the operation of the high gain linear amplifier. Failure to provide the bypass may impair the switching property.

The total lead length between capacitor and coupler should not exceed 1 cm.

Switching Characteristics

(Unless otherwise specified, $T_a = -40$ to 105°C , $V_{CC} = 4.5$ to 5.5V)


Characteristic	Symbol	Test Circuit	Conditions		Min	Typ.	Max	Unit	
Propagation delay time to logic high \rightarrow Low output	t_{pHL}	5	$V_{IN} = 0 \rightarrow 5\text{V}$	$R_{IN} = 360\Omega$ $C_{IN} = 22\text{pF}$ $V_L = 0\text{V}$ (Note 1)	—	—	30	ns	
Propagation delay time to logic low \rightarrow High output	t_{pLH}		$V_{IN} = 5 \rightarrow 0\text{V}$		—	—	30	ns	
Switching time dispersion between ON and OFF	$ t_{pHL} - t_{pLH} $		$V_{IN} = 5\text{V}$		—	—	10	ns	
Output fall time (90-10%)	t_f		$V_{IN} = 0 \rightarrow 5\text{V}$		—	3	—	ns	
Output rise time (10-90%)	t_r		$V_{IN} = 5 \rightarrow 0\text{V}$		—	2	—	ns	
Propagation delay time to logic high \rightarrow Low output	t_{pHL}	6	$V_{IN} = 1.1 \rightarrow 5\text{V}$	$R_{IN} = 360\Omega$ $C_{IN} = 22\text{pF}$ $V_L = 1.1\text{V}$ (Note 1)	—	—	20	ns	
Propagation delay time to logic low \rightarrow High output	t_{pLH}		$V_{IN} = 5 \rightarrow 1.1\text{V}$		—	—	20	ns	
Propagation delay skew	T_{psk}		—		—	—	16	ns	
Switching time dispersion between ON and OFF	$ t_{pHL} - t_{pLH} $		—		—	2	8	ns	
Output fall time (90-10%)	t_f		$V_{IN} = 1.1 \rightarrow 5\text{V}$		—	3	—	ns	
Output rise time (10-90%)	t_r		$V_{IN} = 5 \rightarrow 1.1\text{V}$		—	3	—	ns	
Data rate	T		—		—	50	—	MBd	
Common mode transient immunity at high Level output	CM_H	7	$V_{CM} = 1000\text{V}_{\text{p-p}}$, $T_a = 25^\circ\text{C}$ $I_F = 0\text{mA}$, $V_{CC} = 5\text{V}$, $V_O(\text{Min}) = 4\text{V}$		10000	—	—	$\text{V}/\mu\text{s}$	
Common mode transient immunity at low level output	CM_L		$V_{CM} = 1000\text{V}_{\text{p-p}}$, $T_a = 25^\circ\text{C}$ $I_F = 10\text{mA}$, $V_{CC} = 5\text{V}$, $V_O(\text{Max}) = 0.4\text{V}$		-10000	—	—	$\text{V}/\mu\text{s}$	

*All typical values are at $T_a = 25^\circ\text{C}$, $V_{CC} = 5\text{V}$.


Note : This product has an automatic threshold control (ATC) circuit in order to reduce input current dependence of its switching time. The ATC circuit may not be able to respond accordingly when an input signal is driven after a prolonged absence of signals to the product. As a result, switching operation, pertaining to the first pulse of an input signal, could be unstable. Theoretically however, stable switching operation should be achievable from the second pulse onwards. As such, please check the switching operation and take the appropriate measures when designing applications in which this product shall be used.

Note 1: CL is approximately 15pF which includes probe and Jig/stray wiring capacitance.


TEST CIRCUIT 1: VOL




TEST CIRCUIT 2: V_{OH}





TEST CIRCUIT 3: ICCL




TEST CIRCUIT 4: ICCH




TEST CIRCUIT 5: tpHL , tpLH





TEST CIRCUIT 6: tpHL , tpLH



(example for LED drive circuit)



TEST CIRCUIT 7: Common-Mode Transient Immunity Test Circuit



$$CM_H = \frac{800(V)}{t_r(\mu s)} \quad CM_L = -\frac{800(V)}{t_f(\mu s)}$$

RESTRICTIONS ON PRODUCT USE

- Toshiba Corporation, and its subsidiaries and affiliates (collectively "TOSHIBA"), reserve the right to make changes to the information in this document, and related hardware, software and systems (collectively "Product") without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. **TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.**
- **PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT ("UNINTENDED USE").** Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, devices related to electric power, and equipment used in finance-related fields. **IF YOU USE PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT.** For details, please contact your TOSHIBA sales representative.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- **ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.**
- GaAs (Gallium Arsenide) is used in Product. GaAs is harmful to humans if consumed or absorbed, whether in the form of dust or vapor. Handle with care and do not break, cut, crush, grind, dissolve chemically or otherwise expose GaAs in Product.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. **TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.**