samtec

TIGER EYE™ DISCRETE



(1,27 mm) .050"

TFSS, TFSST, TFSD, TFSDT SERIES

TIGER EYE™ DISCRETE CABLE ASSEMBLY

SPECIFICATIONS

For complete specifications see www.samtec.com?TFSS, www.samtec.com?TFSD, www.samtec.com?TFSDT, or www.samtec.com?TFSST

Insulator Material:
Black LCP
Contact Material:
BeCu
Plating:
Au over 50µ" (1,27 µm) Ni
Operating Temp Range:
-10°C to +80°C (PVC)
-40°C to +125°C (*Teflon®)
Wire:
28 or 30 AWG
RoHS Compliant:
Yes

Mates with:
SFM, SFC (–TR requires TFM–WT option), SFML (–XL end option required)



RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality

FILE NO. E111594

ALSO AVAILABLE (MOQ Required)

- Color coded cable (*Teflon® N/A)
- Other plating options

Contact Samtec.

*DuPont™ Teflon® is a registered trademark of the E.I. du Pont de Nemours and Company or its affiliates.

Note: For wiring option and pin position location information, refer to drawings on web.

Note: Some lengths, styles and options are non-standard, non-returnable.

TYPE STRIP	POSITIONS PER ROW	WIRE GAUGE	PLATING OPTION	ASSEMBLED LENGTH	END OPTION	END 2 OPTION
TFSS = Single Row PVC Cable **TFSST** = Single Row *Teflon® Cable **TFSD** = Double Row PVC Cable **TFSDT** = Double Row *Teflon® Cable	–03, –04, –05, –07, –10, –15, –20, –25, –40, –50 (Standard sizes)	–30 = 30 AWG –28 = 28 AWG	–G = 10µ" (0,25 µm) Gold on contact	–"XX.XX" = Assembled Length in Inches (76,20 mm) 03.00" min. for –S end option (82,60 mm) 03.25" min. for –D end option	–S = Single Ended –D = Double Ended –T = Transfer End Terminal on End 1 Socket on End 2 (See chart for End 2 option) –TF* = Transfer End with Friction Lock –TR = Transfer End with Retention Latch (TFM –WT option required for mating) *–05 & –07 positions not available. TFSD, TFSDT only	Requires –D, –TF or –TR (End 1 Notch Down). –NUS = Notch up, straight (Pin 1 to Pin 2) –NDS = Notch down, straight (Pin 1 to Pin N-1) –NUX = Notch up, crossed (Pin 1 to Pin 1) (TFSD/ TFSDT only) –NDX = Notch down, crossed (Pin 1 to Pin N) (TFSD/ TFSDT only)

END 2	END OPTION
T-NUS	Pin 1 to Pin N
T-NDS	Pin 1 to Pin 1
T-NUX	Pin 1 and Pin N-1
T-NDX	Pin 1 to Pin 2



Due to technical progress, all designs, specifications and components are subject to change without notice.