



Inventek Systems
Embedding Connectivity Everywhere

Inventek Systems

ISM4319-M3X-L44-X

Embedded Serial-to-Wi-Fi Module

eS-WiFi™

802.11 b/g/n

Data Sheet



ISM4319-M3X Product Specification

Table of Contents

1	GENERAL DESCRIPTION	4
2	PART NUMBER DETAIL DESCRIPTION	5
2.1	Ordering Information	5
3	GENERAL FEATURES	5
3.1	Limitations	6
3.2	Regulatory Compliance	6
3.3	FCC User's Manual Statements:	7
3.4	Industry Canada User's Manual Statements:	8
4	COMPLIMENTARY DOCUMENTATION	9
4.1	Inventek Systems	9
5	SPECIFICATIONS	9
5.1	Module Architecture	9
5.2	External Antenna Connections	10
5.3	Mechanical Specifications (Keep out)	10
5.4	Mechanical Specifications (Continued)	11
5.5	Environmental Specifications	11
6	HARDWARE ELECTRICAL SPECIFICATIONS	11
6.1	Absolute Maximum Ratings	11
6.2	Recommended Operating Ratings	11
6.3	Power Consumption	12
6.3.1	Estimate Power Consumption	12
6.3.2	Stop Mode	12
7	Pin out	13
7.1.1	Detailed Pin Description	14
7.1.2	Configuration Pins:	15
7.2	RF Specification	16
7.3	RF Specification (Continued)	17
8	Antenna Patterns	17
8.1	External Antenna	17
8.2	PCB Etch antenna gain on the evaluation board	18
8.3	Farfield Directivity	19
9	On Board Processor	20
10	ISM4319-M3-L44 FOOTPRINT	21
10.1	Module's package dimensions (mm)	21
11	Typical Application Circuit	22
11.1	Reference Schematic (EVB)	23

11.2	USB to UART	24
11.3	Connecting Microcontroller to eS-WiFi UART	25
11.4	JTAG and Reset Connections	26
11.5	eS-WiFi Programming Options	27
11.6	eS-WiFi USB Direct Connection Option.....	27
12	Product Compliance Considerations	28
13	Reflow Profile	28
14	Packaging Information.....	29
14.1	MSL Level / Storage Condition.....	29
14.2	Module's Assembly Instructions	30
15	REVISION CONTROL	30
16	CONTACT INFORMATION.....	30

1 GENERAL DESCRIPTION

The Inventek ISM4319-M3x-L44 is an embedded (eS-WiFi™) serial-to-WiFi wireless internet connectivity device. The Wi-Fi module hardware consists of an M3 Cortex host processor, integrated antenna (or optional ext. antenna) and Broadcom Wi-Fi device. The module provides USB, SPI and UART interfaces enabling connection to an embedded design. The Wi-Fi module requires no operating system and has a completely integrated TCP/IP Stack that only requires a simple AT command set to establish connectivity for your wireless product, minimizing development time, testing routines and certification. The low cost, small footprint (14.5 x 30 mm or 14.5 x 28mm) and ease of use make it ideal for a range of embedded wireless applications.

Summary of Key Features:

- 802.11 b/g/n compliant based on Broadcom MAC/Baseband/Radio device.
- Fully contained TCP/IP stack minimizing host CPU requirements.
- Configurable through AT commands.
- Host interface: UART, SPI, or USB.
- Network features ICMP (Ping), ARP, DHCP, TCP, UDP.
- Low power operation (3.3V supply) with built-in low power modes.
- Secure Wi-Fi authentication WEP-128, WPA-PSK (TKIP), WPA2-PSK.
- Connects with different vendors' b/g/n Access Points in the Wireless LAN.

Typical Applications:

- PDA, Pocket PC, computing devices
- Building automation and smart energy control.
- Industrial sensing and remote equipment monitoring.
- Warehousing, logistics and freight management
- PC and gaming peripherals
- Printers, scanners, alarm and video systems
- Medical applications including patient monitoring and remote diagnostics

2 PART NUMBER DETAIL DESCRIPTION

2.1 Ordering Information

Device	Description	Ordering Number
ISM4319-M3-L44	802.11 Module, STM32F103 (512K), Commercial Temp (UART,SPI, Internal Etch Antenna)	ISM4319-M3-L44-E
ISM4319-M3-L44	802.11 Module, STM32F103 (512K), Commercial Temp (UART,SPI, External U.fl Antenna)	ISM4319-M3-L44-U
ISM4319-M3E-L44	802.11 Module, STM32F205 (512K), Commercial Temp (UART,SPI, Internal Etch Antenna)	ISM4319-M3E-L44-E
ISM4319-M3G-L44	802.11 Module, STM32F103 (1 Meg), Commercial Temp (UART,SPI, Internal Etch Antenna)	ISM4319-M3G-L44-E
ISM4319-M3-EVB-UC	Evaluation Board, USB cable with ISM4319-M3-L44-U/C, Quick Start Guide	ISM4319-M3-EVB-UC
ISM4319-M3G-EVB-E	Evaluation Board, USB cable with ISM4319-M3G-L44-E, Quick Start Guide	ISM4319-M3G-EVB-E

3 GENERAL FEATURES

- Based on the Broadcom BCM4319
- CPU ARM Cortex™-M3 32-bit RISC core from ST Microelectronics
- Host UART, SPI or USB interface
- IEEE 802.11n D7.0 -OFDM-72.2 Mbps -single stream w/20 Mhz, Short GI
- IEEE 802.11g (OFDM 54 Mbps)
- IEEE 802.11b (DSSS 11Mbps)
- IEEE 802.11i (Security)
 - WPA (Wi-Fi Protected Access) –PSK/TKIP
 - WPA2 (Wi-Fi Protected Access 2)- AES/CCMP/802.1x Authentication
- Inputs +3.3 V tolerant
- 5 GPIO, 5 ADC
- The devices operate from a 2.0 to 3.6 V power supply
- -35 to +85 °C temperature range
- Power-saving mode allows the design of low-power applications
- Lead Free Design which is compliant with ROHS requirements
- EMI/EMC Metal Shield for best RF performance in noisy environments and to accommodate for lower RF emissions/signature for easier FCC compliance
- FCC/CE Compliance Certified

3.1 Limitations

Inventek Systems products are not authorized for use in safety-critical applications (such as life support) where a failure of the Inventek Systems product would reasonably be expected to cause severe personal injury or death.

3.2 Regulatory Compliance



Regulator	Device ID
FCC	FCC ID: O7P-ISM4319F1
IC	10147A-ISM4319F1
CE	Compliant
RoHS	Compliant

The ISM4319F1 is the Inventek part number for the Broadcom BCM4319 Wi-Fi radio SIP.

3.3 FCC User's Manual Statements:

Antenna Installation requirements- *The antenna(s) used for this transmitter must be installed to provide a separation distance of at least 20 cm from all persons and must not be co-located or operating in conjunction with any other antenna or transmitter.*

Manufacturer	Type of Antenna	Model	Gain dB	Type of Connector
Inventek	U.Fl port Antenna	W24-SSMA-M	2.15	Unique Connector
Pulse Technology	Surface Mount	W3043	1.85 (4 dBic)	Permanent integral
Inventek	Trace Antenna	NA	0	Permanent integral

FCC Notice-

This device complies with Part 15 of the FCC rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications.

However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.*
- Increase the separation between the equipment and receiver.*
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.*
- Consult the dealer or an experienced radio/TV technician for help.*

(15.21) FCC Statement: Warning: changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate this equipment.

3.4 Industry Canada User's Manual Statements:

IC RSS-210/RSS-Gen Notices-

Operation is subject to the following two conditions: (1) this device may not cause interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device.

L'opération est soumise aux deux conditions suivantes: (1) cet appareil ne peut pas provoquer d'interférences et (2) cet appareil doit accepter toute interférence, y compris les interférences qui peuvent causer un mauvais fonctionnement de l'appareil.

Under Industry Canada regulations, this radio transmitter may only operate using an antenna of a type and maximum (or lesser) gain approved for the transmitter by Industry Canada. To reduce potential radio interference to other users, the antenna type and its gain should be so chosen that the equivalent isotropically radiated power (*e.i.r.p.*) is not more than that necessary for successful communication.

Sous la réglementation d'Industrie Canada, ce transmetteur radio ne peut fonctionner en utilisant une antenne d'un type et un maximum (ou moins) gain approuvées pour l'émetteur par Industrie Canada. Pour réduire le risque d'interférence aux autres utilisateurs, le type d'antenne et son gain doivent être choisis de manière que la puissance isotrope rayonnée équivalente (PIRE) ne dépasse pas ce qui est nécessaire pour une communication réussie.

This radio transmitter 6546A-VN3104034R5 has been approved by Industry Canada to operate with the antenna types listed above with the maximum permissible gain and required antenna impedance for each antenna type indicated. Antenna types not included in this list, having a gain greater than the maximum gain indicated for that type, are strictly prohibited for use with this device.

Cet émetteur de radio 6546A-VN3104034R5 a été approuvé par Industrie Canada pour fonctionner avec les types d'antennes énumérées ci-dessus avec le gain maximal admissible et impédance d'antenne requise pour chaque type d'antenne indiqué. Types d'antennes ne figurent pas dans cette liste, ayant un gain supérieur au gain maximum indiqué pour ce type, sont strictement interdites pour l'utilisation avec cet appareil.

PRELIMINARY


4 COMPLIMENTARY DOCUMENTATION

4.1 Inventek Systems

- Evaluation Board
 - ISM4319-M3x-EVB Evaluation Board Specification
 - EVB Users Guide
 - Quick Start Guide
 - eS-WiFi Demo software (includes EVB Drivers and Firmware)
- At Command Set
 - AT Command Set User's Manual
 - AT Command Set Quick Reference Guide
- Firmware
- OrCAD Schematic Symbol
- PADS Land Pattern
- ISM4319x specification and Product Brief
- FCC Test Report
- NDA/ SLA documents

5 SPECIFICATIONS

5.1 Module Architecture



- Note:
1. ADC1-ADC4 can also be used as SPI port
 2. Antenna Options: Integrated microstrip antenna or U.fl connector for an external antenna.

5.2 External Antenna Connections

ISM4319-M3x-L44-U module is designed for use with an external antenna via a connection using the U.FL connector.

Item	Description
Connector	U.FL series
Manufacturer	I-PEX Co., Ltd.
Part No.	20279-001E-01
Height	1.25 mm
Width	2 mm
DC	3.0 – 5.0 V

Table 1 On-Board Antenna Connector

5.3 Mechanical Specifications (Keep out)

The Physical dimensions of this GPS Module are as follow (Arrow points to antenna keep out Area)




Figure 2: ANTENNA IS IN ETCH

5.4 Mechanical Specifications (Continued)

Items	Description ISM4319-M3x-L44-E (**Antenna in Etch)	Description ISM4319-M3-L44-U (* External Antenna)
Length	30 mm (-/+0.5 mm)	28 (-/+0.5 mm)
Width	14.5 (-/+0.5 mm)	14.5 (-/+0.5 mm)
Height	2.5 ± 0.2 mm	2.5 ± 0.2 mm
Package	44 pin LGA	44 pin LGA

* External Antenna does not require keep out Area

** Keep out Area should ideally have the antenna handing off the side of the PCB for best performance.

***The ISM4319-M3x-L44 U and E have the same footprint but the “U” is 2mm shorter in length.

5.5 Environmental Specifications

Item	Description
Operating temperature range	-35 deg. C to +85 deg. C
Storage temperature range	-40 deg. C to +85 deg. C
Humidity	95% max non-condensing

Note 1: The ISM4319-M3X supports a functional operating range of -35°C to +80°C. However the optimal RF performance specified in this data sheet is only guaranteed for temperatures from -10°C to +65°C

6 HARDWARE ELECTRICAL SPECIFICATIONS

6.1 Absolute Maximum Ratings

Symbol	Description	Min	Max	Unit
VDD	Input supply Voltage	-0.4	3.7	V
VBAT	Battery Backup	-0.4	3.6	V

6.2 Recommended Operating Ratings

Symbol	Min.	Typ.	Max.	Unit.
VDD	3.0	3.3	3.6	V
VBAT	3.0	3.3	3.6	V

6.3 Power Consumption

6.3.1 Estimate Power Consumption

Test conditions: VDD=3.3V; VDDIO=3.3V Temp=25°C.
 1460 Bytes @ UART 115,200 baud – Low Power

Mode/Description	802.x	Voltage	Typ. (RMS)	Max.	Unit
Running Full Power ⁽¹⁾	/n	3.3V	110		mA
Running in Power Save Mode	/n	3.3V	55	110 ⁽¹⁾	mA
Wi-Fi Radio Off	b/g/n		30		mA
Stop Mode ⁽²⁾			tbd		uA

Note:

⁽¹⁾ During transmit the max can reach 340 mA burst of not more than 5ms.


⁽²⁾ Available in Firmware release 1.3 or later only.

The eS-WiFi modules support multiple power saving modes. Please see the power savings application note for more detailed information

6.3.2 Stop Mode

Stop Mode is initiated by software and exited by the Wakeup pin. (Wakeup pin is 3.5 volt tolerant). The wakeup pin is an external interrupt pin that on the rising edge will cause the module to exit stop mode. It is an edge triggered input. It is critical to have no glitch on this line.

7 Pin out



7.1.1 Detailed Pin Description

Pin No.	Type	Pin Definition	Descriptions
1	G	GND	Ground
2	I	VDD	3.3V
3	G	GND	Ground
4	I/O	RES	Reserved
5	I/O	RES	Reserved
6	I/O	RES	Reserved
7	I/O	RES	Reserved
8	I/O	RES	Reserved
9	I	ADC 4 / SPI_MOSI	ADC Input Pins Note: ADC1-ADC4 can be used as SPI port. (Refer to Table 7.1.2)
10	I	ADC 3 / SPI_MISO	
11	I	ADC 2 / SPI_SCK	
12	I	ADC 1 / SPI_NSS	
13	I	ADC 0	
14	I	VDD	3.3V
15	I	VBAT	3.3V
16	O	Wakeup	(Refer to Section 6.3.2)
17	G	GND	Ground
18	I	DP	USB Data Plus (Refer to Table 7.1.2)
19	I/O	DM	USB Data Minus (Refer to Table 7.1.2)
20	G	GND	Ground
21	I/O	RX	UART Receive (Refer to Table 7.1.2)
22	I/O	TX	UART Transmit (Refer to Table 7.1.2)
23	I/O	GPIO 0	General Purpose Interface Pins
24	I/O	GPIO 1	
25	I/O	GPIO 2	
26	I/O	GPIO 3	
27	I/O	GPIO 4	
28	I	CFG0	Configuration Pin 0 (Refer to Table 7.1.2)
29	I	CFG1	Configuration Pin 1 (Refer to Table 7.1.2)
30	O	RES	Reserved
31	I	RES	Reserved
32	I	RES	Reserved
33	I	RES	Reserved
34	I	RSTN	Reset
35	G	GND	Ground
36	G	GND	Ground

Pin No.	Type	Pin Definition	Descriptions
37	G	GND	Ground
38	G	GND	Ground
39	G	GND	Ground
40	G	GND	Ground
41	G	GND	Ground
42	G	GND	Ground
43	G	GND	Ground
44	G	GND	Ground

7.1.2 Configuration Pins:

CFG0	CFG1	Internally Pulled High
1	1	UART (NC)
1	0*	SPI
0*	1	USB VCP
0*	0*	USB HID

*Requires a 10K ohm pull down

Wi-Fi RF Specification

7.2 RF Specification

Conditions: VDD=3.3V; VDDIO=3.3V; TEMP: 25°C

Feature	Description
WLAN Standard	IEEE 802.11b/g/n, Wi-Fi compliant
Frequency Range	2.400 GHz ~ 2.497 GHz (2.4 GHz ISM Band)
Number of Channels	Ch1 ~ Ch14
Modulation	802.11 g/n : OFDM /64-QAM,16-QAM, QPSK, BPSK 802.11b : CCK, DQPSK, DBPSK
Output Power	802.11b /11Mbps : 15 dBm $\pm$ 1.5 dB
	802.11g /54Mbps: 15 dBm $\pm$ 1.5 dB @ EVM $\leq$ -25dB
	802.11n /72Mbps: 13 dBm $\pm$ 1.5 dB @ EVM $\leq$ -28dB
Receive Sensitivity (11n,20MHz) @10% PER	- MCS=0 PER @ -86 dBm, typical
	- MCS=1 PER @ -85 dBm, typical
	- MCS=2 PER @ -85 dBm, typical
	- MCS=3 PER @ -84 dBm, typical
	- MCS=4 PER @ -80 dBm, typical
	- MCS=5 PER @ -78 dBm, typical
	- MCS=6 PER @ -72 dBm, typical
	- MCS=7 PER @ -69 dBm, typical
Receive Sensitivity (11g) @10% PER	- 6Mbps PER @ -89 dBm, typical
	- 9Mbps PER @ -88 dBm, typical
	- 12Mbps PER @ -88 dBm, typical
	- 18Mbps PER @ -87 dBm, typical
	- 24Mbps PER @ -83 dBm, typical
	- 36Mbps PER @ -80 dBm, typical
	- 48Mbps PER @ -75 dBm, typical
	- 54Mbps PER @ -72 dBm, typical
Receive Sensitivity (11b) @10% PER	- 1Mbps PER @ -93 dBm, typical
	- 2Mbps PER @ -91 dBm, typical
	- 5.5Mbps PER @ -89 dBm, typical
	- 11Mbps PER @ -87 dBm, typical
Data Rates	802.11b : 1, 2, 5.5, 11Mbps
	802.11g : 6, 9, 12, 18, 24, 36, 48, 54Mbps

7.3 RF Specification (Continued)

Feature	Description
Data Rate (20MHz ,Long GI,800ns)	802.11n: 6.5, 13, 19.5, 26, 39, 52, 58.5, 65Mbps
Feature	Description
Data Rate (20MHz ,short GI,400ns)	802.11n : 7.2, 14.4, 21.7, 28.9, 43.3, 57.8, 65,72.2Mbps
Maximum Input Level	802.11b : -10 dBm
	802.11g : -10 dBm

8 Antenna Patterns

The eS-Wifi family of Wifi products comes with three different antenna offerings:

ISM4319-M3-L44-E	PCB Etch Antenna
ISM4319-M3-L44-U	U.FL connector for external antenna
ISM4319-M3-L44-C	Ceramic Antenna

8.1 External Antenna

The U.fl antenna that has passed FCC and CE certified can be found on the Inventek Website. The part number is W24-SSMA-M. It is a 2.4 GHz straight SMA Male antenna and we sell an adapter that plugs directly on the eS-Wifi- to SMA (U.fl – SMA Adapter).



Wi-Fi 2.4Ghz SMA Male




W24-SSMA-M


8.2 PCB Etch antenna gain on the evaluation board

The es-Wi-Fi PCB etch antenna performance is shown below. This etch antenna has been FCC and CE certified and the radiation patterns shown below are based on simulation using our evaluation boards that has a ground plane 71 x 48mm.



8.3 Farfield Directivity





9 On Board Processor

The eS-WiFi module is available with ST Microcontrollers, the F103 and F205 family of processors. Inventek will support the microcontroller that best fits your performance and feature requirements.


ISM4319-M3-L44	STM32F103 - 512K Flash Microcontroller,	ISM4319-M3-L44-E
ISM4319-M3-L44	STM32F103 - 512K Flash Microcontroller	ISM4319-M3-L44-U
ISM4319-M3E-L44	STM32F205 (512K), Flash Microcontroller	ISM4319-M3E-L44-E
ISM4319-M3G-L44	STM32F103 (1Meg), Flash Microcontroller)	ISM4319-M3G-L44-E

See the STM32F103RE or the STM32F205 specification from ST Microelectronics for UART, SPI (Slave Mode) and USB Device.

<http://www.st.com/internet/mcu/product/164485.jsp#DATASHEET>


10 ISM4319-M3-L44 FOOTPRINT

10.1 Module's package dimensions (mm)




11 Typical Application Circuit


This is the minimum number of wires required to be connected to your microcontroller for operation in UART mode. You may also want to bring out the JTAG lines for firmware upgrades.




11.1 Reference Schematic (EVB)




11.2 USB to UART




11.3 Connecting Microcontroller to eS-WiFi UART



11.4 JTAG and Reset Connections




11.5 eS-WiFi Programming Options



11.6 eS-WiFi USB Direct Connection Option

(Contact Inventek for this mode)



12 Product Compliance Considerations


RoHS: Restriction of Hazardous Substances (RoHS) directive has come into force since 1st July 2006 all electronic products sold in the EU must be free of hazardous materials, such as lead. Inventek is fully committed to being one of the first to introduce lead-free GPS products while maintaining backwards compatibility and focusing on a continuously high level of product and manufacturing quality.

EMI/EMC: The Inventek module design embeds EMI/EMC suppression features and accommodations to allow for higher operational reliability in noisier (RF) environments and easier integration compliance in host (OEM) applications.

FCC/CE: The module will be in compliance test for FCC/CE

13 Reflow Profile

- Reference the IPC/JEDEC standard.
- Peak Temperature: $<250^{\circ}\text{C}$
- Number of Times: ≤ 2 times



14 Packaging Information

14.1 MSL Level / Storage Condition

	Caution This bag contains MOISTURE-SENSITIVE DEVICES Do not open except under controlled conditions - Calculated shelf life in sealed bag: 12 months at $< 40^{\circ}\text{C}$ and $< 90\%$ relative humidity (RH) - Peak package body temperature: 225°C ☐ 240°C ☐ 250°C ☒ 260°C ☐ - After bag is opened, devices that will be subjected to reflow solder or other high temperature process must - Mounted within: 48 hours of factory conditions $< 30^{\circ}\text{C} / 60\% \text{ RH}$, OR - Stored at $< 10\% \text{ RH}$ - Devices require bake, before mounting, if: - Humidity Indicator Card is $> 10\%$ when read at $23 \pm 5^{\circ}\text{C}$ 3a or 3b not met - If baking is required, devices may be baked for 24 hours at $125 \pm 5^{\circ}\text{C}$ Note : If device containers cannot be subjected to high temperature or shorter bake times are desired, reference IPC/JEDEC J-STD-033 for bake procedure Bag Seal Date: <u>See-SEAL DATE LABEL</u> Note: Level and body temperature defined by IPC/JEDEC J-STD-020	LEVEL 4
---	--	--

14.2 Module's Assembly Instructions

Board Placement: The ISM4319-M3-L44 has an optional on board Wi-Fi antenna. The board is designed to be a stuffing option. If you elect to use the on board antenna, then board placement is critical in your system. Several key things to consider when placing the module are:

- Ensure that the antenna portion of the design is placed so that the antenna has no ground plane under, above or near the antenna. Ideally, the antenna requires clear sky for optimal performance. If you have shields or other material around the antenna, please test for interference and loss of signal strength.

15 REVISION CONTROL

Document : ISM4319-M3-L44	Wi-Fi module
External Release	DOC-DS-20023

Date	Author	Revision	Comment
9/17/2011	FMT	1.0	Preliminary
1/23/2012	FMT	2.6	Update P/N, Ref. Schematic
3/14/2012	MFT	2.7	Added Antenna & G model, Typo
3/27/2012	FMT	2.8	Added FCC statement
11/1/2012	FMT	3.0	Updated SPI, Power

16 CONTACT INFORMATION

Inventek Systems
2 Republic Road
Billerica Ma, 01862
Tel: 978-667-1962
Sales@inventeksys.com

www.inventeksys.com

Inventek Systems reserves the right to make changes without further notice to any products or data herein to improve reliability, function, or design. The information contained within is believed to be accurate and reliable. However Inventek Systems does not assume any liability arising out of the application or use of this information, nor the application or use of any product or circuit described herein, neither does it convey any license under its patent rights nor the rights of others.

Copyright (c) 2001-2004 Swedish Institute of Computer Science.
All rights reserved.
www.freertos.org