








PC board drilling dimensions
(after plating – thickness: 1.60 to 3.20 mm)



ROHS PART NUMBER	
PART NUMBER	
200 Mating	D50P91C4GV00LF
500 Mating	D50P91C6GV00LF

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

mat'l. code				surface 		tolerance		projection		product family		
				ISO 1302		ISO 406 ISO 1101				D-SUB		
ltr	ecn no	dr	date	tolerances unless otherwise specified						title		
E	LS06-0074	MPE	2006-05-09	angles	linear	.0±0.1			MALE CONNECTOR DELTA D 50 STRAIGHT PRESS FIT			
F	LS06-0097	LGO	2006-07-29			.00±0.1						
G	LS06-0140	LGO	2006-09-22			.000±0.1						
				0°±2°				scale 2:1				
H	111-0062	MINI	2011-04-04	dr	PESSON	1995-10-03		Amphenol FCi	dwg no		sheet 1 of 1	size
J	ELX-I-24020	AAB	2016-06-06	engr	MITHUN PAUL	2016-06-06			C01-8646-0256		A3	
				chr	ATHUL A.B	2016-06-06						
				appd	BIJU K PAUL	2016-06-06				type Product Customer Drawing		
sheet index	revision	J										
	sheet	1										