

Precision

Digital Step Attenuator

TOAT-R512

50Ω TTL Control, Pin Diode 10 to 1000 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 125°C
Input Power	15 dBm
DC Voltage	5.5 V
TTL	5.5V

Pin Connections

RF IN	4
RF OUT	11
TTL CONTROL #1	2
TTL CONTROL #2	3
TTL CONTROL #3	1
+5V DC	12
CASE GROUND	5,6,7,8,9,10

Features

- wideband, 10 to 1000 MHz
- excellent step accuracy, 0.2 dB typ.
- excellent VSWR 1.3 typ.
- low DC current, 6 mA typ.
- hermetic, metal, TO-8 case

Applications

- base stations
- cellular
- test-sets
- military, hi-rel applications



CASE STYLE: QQ96
PRICE: \$64.45 ea. QTY (1-9)

Digital Step Attenuator Electrical Specifications


MODEL NO.	FREQUENCY (MHz)		PRIMARY ATTENUATION STEPS (dB)			ATTENUATION (dB)		VSWR (:1)		
	f_L	f_U	#1	#2	#3	(1,1,1)** Nom.	(0,0,0) Max.	L	M	U
TOAT-R512	10	1000	0.5±0.18	1±0.25	2±0.25	3.5	4.0	1.6	1.4	1.5

L=10 to 100 MHz M=100 to 500 MHz U=500 to 1000 MHz

** Total attenuation above thru-loss.

1. Step accuracy is specified for basic steps. For combination of steps accuracy is additive.
2. Thru-loss is minimum insertion loss with all attenuation elements bypassed (All TTL controls state are Low)
3. For optimum operation of TOAT models, ensure the device case is properly connected to the ground plane (of PC board)

Outline Drawing






NOTE: PIN NUMBERS DO NOT
APPEAR ON UNIT,
FOR REFERENCE ONLY.

Outline Dimensions (inch/mm)

A	B	C	D	E	F
.600	.250	.25	.016	.020	.04
15.24	6.35	6.35	0.41	0.51	1.02
G	H	J	K		wt
.400	.200	.200	.100		grams
10.16	5.08	5.08	2.54		4.0

Additional Specifications

DC Voltage	+5V
DC Current	12mA max.
Switching Time (50% TTL to within specified accuracy of the next-selected attenuation step, and to within 0.1 dB of steady-state Thru-Loss)	10μs typ., 15μs max.,
TTL Input High Threshold	2V min
TTL Input Low Threshold	0.8V max.
TTL Toggle Rate	50 kHz typ.
1dB Compression	0 dBm (10-100 MHz) +10 dBm (100-1000MHz)



Step Attenuation* at TTL Control State

FREQ.	000	001	010	011	100	101	110	111
(MHz)	THRU LOSS	(dB)	(dB)	(dB)	(dB)	(dB)	(dB)	(dB)
10.00	2.82	0.48	1.01	1.49	2.01	2.49	3.01	3.51
49.60	2.51	0.47	1.02	1.51	2.00	2.49	3.06	3.53
148.60	2.49	0.48	1.03	1.49	2.01	2.51	3.05	3.50
208.00	2.52	0.49	1.02	1.51	2.00	2.50	3.03	3.48
247.60	2.57	0.49	1.02	1.51	1.98	2.48	3.02	3.50
346.60	2.60	0.50	1.05	1.54	1.98	2.49	3.02	3.51
406.00	2.67	0.52	1.08	1.57	1.98	2.47	3.04	3.53
445.60	2.70	0.48	1.03	1.55	1.97	2.48	3.02	3.51
544.60	2.73	0.50	1.08	1.57	1.96	2.49	3.04	3.54
604.00	2.74	0.53	1.09	1.60	1.96	2.52	3.07	3.57
703.00	2.78	0.53	1.12	1.66	1.98	2.54	3.08	3.61
762.40	2.77	0.54	1.09	1.62	1.97	2.50	3.06	3.57
821.80	2.77	0.52	1.14	1.68	2.01	2.55	3.10	3.66
881.20	2.82	0.55	1.14	1.70	2.02	2.57	3.12	3.70
940.60	2.84	0.57	1.14	1.70	1.99	2.59	3.14	3.73
1000.00	2.81	0.56	1.18	1.71	2.07	2.62	3.18	3.76

INPUT VSWR

FREQ.	001	010	011	100	101	110	111
(MHz)							
10.00	1.26	1.26	1.24	1.27	1.25	1.25	1.23
49.60	1.11	1.10	1.10	1.10	1.10	1.10	1.09
148.60	1.14	1.14	1.14	1.13	1.13	1.13	1.13
208.00	1.17	1.17	1.17	1.15	1.16	1.16	1.16
247.60	1.19	1.20	1.20	1.17	1.18	1.18	1.19
346.60	1.24	1.25	1.25	1.22	1.23	1.23	1.24
406.00	1.27	1.28	1.28	1.24	1.25	1.27	1.27
445.60	1.29	1.30	1.30	1.26	1.27	1.29	1.29
544.60	1.31	1.33	1.33	1.29	1.30	1.32	1.33
604.00	1.32	1.34	1.34	1.30	1.31	1.34	1.34
703.00	1.31	1.34	1.33	1.30	1.31	1.35	1.35
762.40	1.30	1.33	1.33	1.30	1.31	1.34	1.35
821.80	1.28	1.32	1.31	1.29	1.30	1.34	1.34
881.20	1.26	1.30	1.30	1.28	1.28	1.33	1.32
940.60	1.24	1.28	1.27	1.26	1.26	1.31	1.31
1000.00	1.21	1.25	1.25	1.23	1.25	1.29	1.29

OUTPUT VSWR

FREQ.	001	010	011	100	101	110	111
(MHz)							
10.00	1.30	1.27	1.27	1.22	1.21	1.20	1.20
49.60	1.12	1.12	1.12	1.09	1.09	1.09	1.09
148.60	1.15	1.15	1.16	1.12	1.11	1.11	1.11
208.00	1.17	1.18	1.18	1.12	1.13	1.12	1.14
247.60	1.21	1.21	1.21	1.14	1.15	1.15	1.15
346.60	1.26	1.27	1.29	1.18	1.19	1.20	1.20
406.00	1.31	1.33	1.33	1.22	1.23	1.24	1.23
445.60	1.32	1.32	1.34	1.22	1.23	1.25	1.26
544.60	1.36	1.37	1.38	1.25	1.25	1.28	1.28
604.00	1.37	1.39	1.39	1.26	1.26	1.31	1.28
703.00	1.38	1.41	1.41	1.26	1.26	1.29	1.29
762.40	1.36	1.39	1.39	1.28	1.27	1.29	1.29
821.80	1.36	1.39	1.39	1.28	1.26	1.30	1.28
881.20	1.30	1.37	1.37	1.25	1.23	1.27	1.26
940.60	1.31	1.37	1.35	1.23	1.23	1.26	1.26
1000.00	1.28	1.33	1.32	1.22	1.22	1.24	1.26

* Step attenuation above thru-loss (TTL logic 000)