

WF998C0915CE

For Short-range Wireless

■ Features

- SAW filter for specified low power radio.
- A filter with low insertion loss.
- Compact and light.

Pb
Free


RoHS Compliant
Directive 2011/65/EU



■ Specifications

Model		WF998C0915CE		
Item		min.	typ.	max.
Nominal frequency : f ₀ (MHz)		–	915	–
Maximum insertion loss (dB) at 902 to 928 MHz		–	2.0	2.5
Pass-band ripple (dB) 902 to 928 MHz		–	0.8	1.5
Guaranteed attenuation (from the throughlevel)(dB)	0.1 to 800 MHz	50	60	–
	800 to 845 MHz	45	60	–
	845 to 880 MHz	35	50	–
	992 to 1020 MHz	35	50	–
	1020 to 1200 MHz	45	52	–
Operating temperature range (°C)		-30 to +80		
Terminating impedance (Ω)		50		

■ Dimensions



■ Characteristics

