



PM10CZF120

FLAT-BASE TYPE
INSULATED PACKAGE

TERMINAL CODE

1. VUPC	11. VN1
2. UP	12. UN
3. VUP1	13. VN
4. VVPC	14. WN
5. VP	15. FO
6. VVP1	16. P
7. VWPC	17. N
8. WP	18. U
9. VWP1	19. V
10. VNC	20. W



INTERFACE WHICH IS
THE SAME AS
THE U-PHASE

Outline Drawing and Circuit Diagram

Dimensions	Inches	Millimeters
A	3.86±0.04	98.0±1.0
B	3.43±0.02	87.0±0.5
C	2.99	76.0
D	2.30	58.42
E	2.20±0.03	56.0±0.8
F	2.21±0.04	56.0±1.0
G	1.73±0.03	44.0±0.8
J	0.83	21.0
K	0.71±0.04	18.0±1.0
L	0.61	15.5
M	0.55±0.01	14.0±0.3
N	0.56	14.29
P	0.32±0.02	8.0±0.5
Q	0.40	10.16

Dimensions	Inches	Millimeters
R	0.22 Dia.	5.5 Dia.
S	0.24 Rad.	6.0 Rad.
T	0.14	3.5
U	0.12±0.02	3.0±0.5
X	0.1±0.01	2.54±0.3
Y	0.1±0.01	2.54±0.3
Z	0.24	6.0
AA	0.12	3.0
AB	0.69	17.5
AC	0.16	4.0
AD	0.10	2.5
AE	2.76	70.0
AF	0.22	5.5
AG	0.22	5.5



Description:

Mitsubishi Intelligent Power Modules are isolated base modules designed for power switching applications operating at frequencies to 20kHz. Built-in control circuits provide optimum gate drive and protection for the IGBT and free wheel-diode power devices.

Features:

- ☐ Complete Output Power Circuit
- ☐ Gate Drive Circuit
- ☐ Protection Logic
 - Short Circuit
 - Over-Current
 - Over Temperature
 - Under Voltage

Applications:

- ☐ Inverters
- ☐ UPS
- ☐ Motion/Servo Control
- ☐ Power Supplies

Ordering Information:

Example: Select the Complete part number from the table below -i.e. PM10CZF120 is a 1200V, 10 Ampere Intelligent Power Module.

Type	Current Rating Amperes	V _{CES} Volts (x 10)
PM	10	120

PM10CZF120

FLAT-BASE TYPE
INSULATED PACKAGE

Absolute Maximum Ratings, $T_j = 25\text{ }^{\circ}\text{C}$ unless otherwise specified

Ratings	Symbol	PM10CZF120	Units
Junction Temperature	T_j	-20 to 150	$^{\circ}\text{C}$
Storage Temperature	T_{stg}	-40 to 125	$^{\circ}\text{C}$
Case Operating Temperature	T_C	-20 to 100	$^{\circ}\text{C}$
Mounting Torque M5 Mounting Screws	—	1.47 ~ 1.96	N · m
Module Weight (Typical)	—	80	Grams
Supply Voltage Protected by OC and SC ($V_D = 13.5 \sim 16.5\text{V}$, Inverter Part)	$V_{CC(\text{prot})}$	800	Volts
Isolation Voltage (Main Terminal to Baseplate, AC 1 min.)	V_{iso}	2500	Vrms

Control Sector

Supply Voltage (Applied between V_{UP1} - V_{UPC} , V_{VP1} - V_{VPC} , V_{WP1} - V_{WPC} , V_{N1} - V_{NC})	V_D	20	Volts
Input Voltage (Applied between U_P - V_{UPC} , V_P - V_{VPC} , W_P - V_{WPC} , U_N · V_N · W_N - V_{NC})	V_{CIN}	20	Volts
Fault Output Supply Voltage (Applied between F_O and V_{NC})	V_{FO}	20	Volts
Fault Output Current (Sink Current of F_O Terminal)	I_{FO}	20	mA

IGBT Inverter Sector

Collector-Emitter Voltage ($V_D = 15\text{V}$, $V_{CIN} = 15\text{V}$)	V_{CES}	1200	Volts
Collector Current, ($T_C = 25^{\circ}\text{C}$)	I_C	10	Amperes
Peak Collector Current, ($T_C = 25^{\circ}\text{C}$)	I_{CP}	20	Amperes
Supply Voltage (Applied between P-N)	V_{CC}	900	Volts
Supply Voltage, Surge (Applied between P-N,)	$V_{CC(\text{surge})}$	1000	Volts
Collector Dissipation	P_C	62	Watts

PM10CZF120

FLAT-BASE TYPE
INSULATED PACKAGE

Electrical and Mechanical Characteristics, $T_j = 25\text{ }^{\circ}\text{C}$ unless otherwise specified

Characteristics	Symbol	Test Conditions	Min.	Typ.	Max.	Units
Control Sector						
Over Current Trip Level	OC	$-20^{\circ}\text{C} \leq T_j \leq 125^{\circ}\text{C}$, $V_D = 15\text{V}$	15	27	–	Amperes
Short Circuit Trip Level	SC	$-20^{\circ}\text{C} \leq T_j \leq 125^{\circ}\text{C}$, $V_D = 15\text{V}$	–	41	–	Amperes
Over Current Delay Time	$t_{\text{off}}(\text{OC})$	$V_D = 15\text{V}$	–	10	–	μs
Over Temperature Protection	OT	Trip Level	100	110	120	$^{\circ}\text{C}$
	OT_r	Reset Level	–	90	–	$^{\circ}\text{C}$
Supply Circuit Under Voltage Protection	UV	Trip Level	11.5	12.0	12.5	Volts
	UV_r	Reset Level	–	12.5	–	Volts
Supply Voltage	V_D	Applied between $V_{\text{UP1}}\text{--}V_{\text{UPC}}$, $V_{\text{VP1}}\text{--}V_{\text{VPC}}$, $V_{\text{WP1}}\text{--}V_{\text{WPC}}$, $V_{\text{N1}}\text{--}V_{\text{NC}}$	13.5	15.0	16.5	Volts
Circuit Current	I_D	$V_D = 15\text{V}$, $V_{\text{CIN}} = 15\text{V}$, $V_{\text{N1}}\text{--}V_{\text{NC}}$	–	18	25	mA
		$V_D = 15\text{V}$, $V_{\text{CIN}} = 15\text{V}$, $V_{\text{XP1}}\text{--}V_{\text{XPC}}$	–	7	10	mA
Input ON Threshold Voltage	$V_{\text{th(on)}}$	Applied between	1.2	1.5	1.8	Volts
Input OFF Threshold Voltage	$V_{\text{th(off)}}$	$U_P\text{--}V_{\text{UPC}}$, $V_P\text{--}V_{\text{VPC}}$, $W_P\text{--}V_{\text{WPC}}$, $U_N \cdot V_N \cdot W_N\text{--}V_{\text{NC}}$	1.7	2.0	2.3	Volts
PWM Input Frequency	f_{PWM}	3- ϕ Sinusoidal	–	–	15	kHz
Fault Output Current	$I_{\text{FO(H)}}$	$V_D = 15\text{V}$, $V_{\text{FO}} = 15\text{V}$	–	–	0.01	mA
	$I_{\text{FO(L)}}$	$V_D = 15\text{V}$, $V_{\text{FO}} = 15\text{V}$	–	10	15	mA
Minimum Fault Output Pulse Width	t_{FO}	$V_D = 15\text{V}$	1.0	1.8	–	ms

PM10CZF120

FLAT-BASE TYPE
INSULATED PACKAGE

Electrical and Mechanical Characteristics, $T_j = 25^\circ\text{C}$ unless otherwise specified

Characteristics	Symbol	Test Conditions	Min.	Typ.	Max.	Units
IGBT Inverter Sector						
Collector-Emitter Cutoff Current	I_{CES}	$V_{CE} = V_{CES}, V_D = 15\text{V}, T_j = 25^\circ\text{C}$	–	–	1	mA
		$V_{CE} = V_{CES}, V_D = 15\text{V}, T_j = 125^\circ\text{C}$	–	–	10	mA
FwDi Forward Voltage	V_{EC}	$-I_C = 10\text{A}, V_D = 15\text{V}, V_{CIN} = 15\text{V}$	–	2.5	3.5	Volts
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$V_D = 15\text{V}, V_{CIN} = 0\text{V}, I_C = 10\text{A}, T_j = 25^\circ\text{C}$	–	2.7	3.7	Volts
		$V_D = 15\text{V}, V_{CIN} = 0\text{V}, I_C = 10\text{A}, T_j = 125^\circ\text{C}$	–	2.5	3.4	Volts
Inductive Load Switching Times	t_{on}		0.3	0.6	1.3	μs
	t_{rr}	$V_D = 15\text{V}, V_{CIN} = 0 \leftrightarrow 15\text{V},$	–	0.15	–	μs
	$t_{C(on)}$	$V_{CC} = 600\text{V}, I_C = 10\text{A},$	–	0.3	1.0	μs
	t_{off}	$T_j = 125^\circ\text{C}, \text{ Inductive Load}$	–	1.8	3.3	μs
	$t_{C(off)}$		–	0.8	1.5	μs

Thermal Characteristics

Characteristic	Symbol	Condition	Min.	Typ.	Max.	Units
Junction to Case Thermal Resistance	$R_{th(j-c)Q}$	Each IGBT	–	–	2.0	$^\circ\text{C/Watt}$
	$R_{th(j-c)F}$	Each FwDi	–	–	5.5	$^\circ\text{C/Watt}$
Contact Thermal Resistance	$R_{th(c-f)}$	Case to Fin Per Module, Thermal Grease Applied	–	–	0.067	$^\circ\text{C/Watt}$


Recommended Conditions for Use

Characteristic	Symbol	Condition	Value	Units
Supply Voltage	V_{CC}	Applied across P-N Terminals	0 ~ 800	Volts
	V_D	Applied between V_{UP1} - V_{UPC} , V_{N1} - V_{NC} , V_{VP1} - V_{VPC} , V_{WP1} - V_{WPC}	15 ± 1.5	Volts
Input ON Voltage	$V_{CIN(on)}$	Applied between	0 ~ 0.8	Volts
Input OFF Voltage	$V_{CIN(off)}$	$U_P, V_P, W_P, U_N, V_N, W_N$	$4.0 \sim V_D$	Volts
PWM Input Frequency	f_{PWM}	Using Application Circuit	5 ~ 15	kHz
Minimum Dead Time	t_{dead}	Input Signal	≥ 3.0	μs


PM10CZF120

FLAT-BASE TYPE
INSULATED PACKAGE


SATURATION VOLTAGE
CHARACTERISTICS (TYPICAL)




COLLECTOR-EMITTER SATURATION
VOLTAGE CHARACTERISTICS (TYPICAL)




OUTPUT CHARACTERISTICS
(TYPICAL)




SWITCHING TIME VS.
COLLECTOR CURRENT (TYPICAL)




SWITCHING TIME VS.
COLLECTOR CURRENT (TYPICAL)



REVERSE RECOVERY CURRENT VS.
COLLECTOR CURRENT (TYPICAL)




FREE-WHEEL DIODE FORWARD
CHARACTERISTICS (TYPICAL)



PM10CZF120

FLAT-BASE TYPE
INSULATED PACKAGE

TRANSIENT THERMAL
IMPEDANCE CHARACTERISTICS
(Each IGBT)



TRANSIENT THERMAL
IMPEDANCE CHARACTERISTICS
(Each FWDi)

