






PANEL THICKNESS	X dimension
0.75-1.25 [0.030-.049]	19.2-0.1 [7.56]
1.25-2.0 [0.049-.079]	19.4-0.1 [7.64]
2.0-3.0 [0.079-.118]	19.8-0.1 [7.80]




PANEL CUTOOUT
NOT TO SCALE



CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 15A @ 125VAC OR
6A @ 250VAC
5. MATERIALS: Silver Plated Copper Alloy
CONTACTS: Coin Silver, Silver Plated
6. ELECTRIC LIFE: 10,000 cycles
7. CONTACT RESISTANCE: $< 20 \text{ Mega } \Omega$
8. INSULATION RESISTANCE: $> 1000 \text{ Mega } \Omega$
9. DIELECTRIC STRENGTH: $> 1500 \text{ V } 1 \text{ minute}$
 $> 3000 \text{ V between poles}$



				
TITLE				
R1966A BLK BLK GF				
SCALE	DATE	DR	DWG	REV
1.5:1	1/9/95	LC	M301204	B