

## Fuse plug - P-FU 6,3X32-EX - 3046499

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fuse plug, fuse type: Sand filled, connection method: Plug connection, nominal current: 10 A, nom. voltage: 500 V, width: 8.2 mm, fuse type: G / 5 x 20, color: black

### Why buy this product

- Large-surface labeling option
- Test contacts on both sides of the fuse
- Test contacts on both sides of the fuse
- Versions with bipolar error display
- Can be used for overload/short-circuit protection



### Key Commercial Data

Packing unit	10 STK
Minimum order quantity	50 STK
GTIN	 4 046356 919258
GTIN	4046356919258

### Technical data

#### General

Note	Prior to replacing the cartridge fuse, disconnect the fuse connector from the basic terminal block.
Number of levels	1
Color	black
Insulating material	PA
Flammability rating according to UL 94	V0
Area of application	Machine building
	Plant engineering

#### Dimensions

Width	8.2 mm
-------	--------

## Fuse plug - P-FU 6,3X32-EX - 3046499

### Technical data

#### Dimensions

Length	40 mm
--------	-------

#### General

Fuse	G / 5 x 20
Fuse type	Sand filled
Degree of pollution	3
Maximum power dissipation	1.6 W (Short-circuit and overload protection)
Maximum load current	10 A (the current is determined by the fuse used)
Nominal current $I_N$	10 A (the current is determined by the fuse used)
Nominal voltage $U_N$	500 V (if used as fuse terminal block)
	500 V (if used as disconnect terminal block)
Open side panel	No

#### Connection data

Connection method	Plug connection
-------------------	-----------------

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

---

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>