


# □ MN101C94A

<b>Type</b>	MN101C94A (ES (Engineering Sample) available)
<b>ROM (x8-bit)</b>	32 K
<b>RAM (x8-bit)</b>	1 K
<b>Package</b>	QFP044-P-1010F *Lead-free
<b>Minimum Instruction Execution Time</b>	0.10 $\mu$ s (at 4.5 V to 5.5 V, 20 MHz) 0.238 $\mu$ s (at 2.7 V to 5.5 V, 8.39 MHz) 0.477 $\mu$ s (at 2.0 V to 5.5 V, 4.19 MHz)*
	* The lower limit for operation guarantee for flash memory built-in type is 2.5 V.
<b>Interrupts</b>	• RESET • Watchdog • External 0 • External 1 • External 2 • Timer 0 • Timer 1 • Timer 2 • Timer 3 • Timer 4 • Timer 5 • Time base • Serial 0 • A/D conversion finish
<b>Timer Counter</b>	<p>Timer counter 0 : 8-bit <math>\times</math> 1 (square-wave/8-bit PWM output, event count, generation of remote control carrier) Clock source ..... 1/1, 1/4 of system clock frequency; 1/1 of OSC oscillation clock frequency; external clock input Interrupt source ..... coincidence with compare register 0</p> <p>Timer counter 1 : 8-bit <math>\times</math> 1 (square-wave output, event count, synchronous output event) Clock source ..... 1/16, 1/64 of system clock frequency; external clock input Interrupt source ..... coincidence with compare register 1</p> <p>Timer counter 0, 1 can be cascade-connected.</p> <p>Timer counter 2 : 8-bit <math>\times</math> 1 (square-wave/8-bit PWM output, event count, synchronous output event) Clock source ..... 1/1, 1/4 of system clock frequency; external clock input Interrupt source ..... coincidence with compare register 2</p> <p>Timer counter 3 : 8-bit <math>\times</math> 1 (square-wave output, event count, generation of remote control carrier, serial 0 baud rate timer) Clock source ..... 1/4, 1/16 of system clock frequency; 1/1 of OSC oscillation clock frequency; external clock input Interrupt source ..... coincidence with compare register 3</p> <p>Timer counter 2, 3 can be cascade-connected.</p> <p>Timer counter 4 : 16-bit <math>\times</math> 1 (square-wave/16-bit PWM output, event count, synchronous output event, input capture) Clock source ..... 1/4, 1/16 of system clock frequency; 1/1 of OSC oscillation clock frequency; external clock input Interrupt source ..... coincidence with compare register 4</p> <p>Time base timer (one-minute count setting, independently operable 8-bit timer counter 5) Clock source ..... 1/4 of system clock frequency; 1/1, 1/8192 of OSC oscillation clock frequency Interrupt source ..... coincidence with compare register 5; 1/8192 prescaler overflow</p> <p>Watchdog timer Interrupt source ..... 1/1048576 of system clock frequency</p>

<b>Serial Interface</b>		Serial 0 : synchronous type/simple UART (half-duplex) × 1 Clock source ..... 1/2, 1/4, 1/16 of system clock frequency; output of timer counter 3										
<b>I/O Pins</b>	<b>I/O</b>	26	<ul style="list-style-type: none"> <li>Common use: 17</li> <li>Specified pull-up resistor available</li> <li>Input/output selectable (bit unit): 26</li> </ul>									
	<b>Input</b>	11	<ul style="list-style-type: none"> <li>Common use</li> <li>Specified pull-up resistor available</li> </ul>									
<b>A/D Inputs</b>		10-bit × 8-ch. (with S/H)										
<b>Special Ports</b>		Buzzer output, remote control carrier signal output, high-current drive port										
<b>Electrical Characteristics</b>												
<b>Supply current</b>												
<b>Parameter</b>	<b>Symbol</b>	<b>Condition</b>	<b>Limit</b>									
			<b>min</b>	<b>typ</b>	<b>Unit</b>							
<b>Operating supply current</b>	IDD1	fosc = 20 MHz, VDD = 5 V		15	40 mA							
	IDD2	fosc = 8.39 MHz, VDD = 5 V		6	18 mA							
<b>Supply current at HALT</b>	IDD3	ffosc = 8.39 MHz, VDD = 5 V, Ta = 25°C		1.2	3 mA							
<b>Supply current at STOP</b>	IDD4	VDD = 5 V, Ta = 25°C			2 µA							
	IDD5	VDD = 5 V, Ta = -40°C to +85°C			20(50) µA							

( ) : Flash memory built-in type

<b>Pin Assignment</b>
-----------------------



QFP044-P-1010F \*Lead-free

## Support Tool

<b>In-circuit Emulator</b>	PX-ICE101C/D+PX-PRB101C94-QFP044-P-1010									
<b>Flash memory Built-in Type</b>	<table><tr><td>Type</td><td>MN101CF94D (ES (Engineering Sample) available)</td></tr><tr><td>ROM (x 8-bit)</td><td>64 K</td></tr><tr><td>RAM (x 8-bit)</td><td>2 K</td></tr><tr><td>Minimum instruction execution time</td><td>0.10 <math>\mu</math>s (at 4.5 V to 5.5 V, 20 MHz) 0.238 <math>\mu</math>s (at 2.7 V to 5.5 V, 8.39 MHz) 0.477 <math>\mu</math>s (at 2.5 V to 5.5 V, 4.19 MHz)</td></tr></table>		Type	MN101CF94D (ES (Engineering Sample) available)	ROM (x 8-bit)	64 K	RAM (x 8-bit)	2 K	Minimum instruction execution time	0.10 $\mu$ s (at 4.5 V to 5.5 V, 20 MHz) 0.238 $\mu$ s (at 2.7 V to 5.5 V, 8.39 MHz) 0.477 $\mu$ s (at 2.5 V to 5.5 V, 4.19 MHz)
Type	MN101CF94D (ES (Engineering Sample) available)									
ROM (x 8-bit)	64 K									
RAM (x 8-bit)	2 K									
Minimum instruction execution time	0.10 $\mu$ s (at 4.5 V to 5.5 V, 20 MHz) 0.238 $\mu$ s (at 2.7 V to 5.5 V, 8.39 MHz) 0.477 $\mu$ s (at 2.5 V to 5.5 V, 4.19 MHz)									
Package	QFP044-P-1010F *Lead-free									

**MN101C94A**

**Request for your special attention and precautions in using the technical information and semiconductors described in this material**

(1) An export permit needs to be obtained from the competent authorities of the Japanese Government if any of the products or technical information described in this material and controlled under the "Foreign Exchange and Foreign Trade Law" is to be exported or taken out of Japan.

(2) The technical information described in this material is limited to showing representative characteristics and applied circuits examples of the products. It neither warrants non-infringement of intellectual property right or any other rights owned by our company or a third party, nor grants any license.

(3) We are not liable for the infringement of rights owned by a third party arising out of the use of the technical information as described in this material.

(4) The products described in this material are intended to be used for standard applications or general electronic equipment (such as office equipment, communications equipment, measuring instruments and household appliances).

Consult our sales staff in advance for information on the following applications:

- Special applications (such as for airplanes, aerospace, automobiles, traffic control equipment, combustion equipment, life support systems and safety devices) in which exceptional quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or harm the human body.
- Any applications other than the standard applications intended.

(5) The products and product specifications described in this material are subject to change without notice for modification and/or improvement. At the final stage of your design, purchasing, or use of the products, therefore, ask for the most up-to-date Product Standards in advance to make sure that the latest specifications satisfy your requirements.

(6) When designing your equipment, comply with the guaranteed values, in particular those of maximum rating, the range of operating power supply voltage, and heat radiation characteristics. Otherwise, we will not be liable for any defect which may arise later in your equipment.

Even when the products are used within the guaranteed values, take into the consideration of incidence of break down and failure mode, possible to occur to semiconductor products. Measures on the systems such as redundant design, arresting the spread of fire or preventing glitch are recommended in order to prevent physical injury, fire, social damages, for example, by using the products.

(7) When using products for which damp-proof packing is required, observe the conditions (including shelf life and amount of time let standing of unsealed items) agreed upon when specification sheets are individually exchanged.

(8) This material may be not reprinted or reproduced whether wholly or partially, without the prior written permission of Matsushita Electric Industrial Co., Ltd.