


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HM	00		S	REVISED PER ECO-12-012703	11JUL2012	GG	JG



- 1

DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2

MATERIAL: HOUSING-POLYCARBONATE,CLEAR.
TERMINAL-0.36[.014] THICK PHOSPHOR BRONZE PLATED WITH 1.27 μ m[.000050] THICK GOLD IN LOCALIZED GOLD PLATE AREA OVER 2.54 μ m[.000100] THICK NICKEL UNDERPLATE.
- 3

PLUG WILL ACCEPT 24 OR 26 AWG SOLID WIRE HAVING A MAXIMUM INSULATION DIAMETER OF 0.89-0.99[.035-.039] AND A MAXIMUM OVAL CABLE JACKET OF 2.54 X 8.89[.100 X .350].
- 4

TERMINATED DIMENSION 6.15[.242] MAXIMUM.
- 6

10,000 ASSEMBLIES PER PACKAGE.
- 7


500 ASSEMBLIES PER PACKAGE.
- 8

100 ASSEMBLIES PER PACKAGE.
- 10

REELED PRODUCT ON STRIP DOES NOT HAVE VOID CORING ILLUSTRATED ON THIS DRAWING.
- 11

100 ASSEMBLIES PER CARTON.

OBSOLETE	8	5-554720-3
	7	5-554720-2
	6	5-554720-1
	11	3-554720-3
	REELED 10	554720-1
	PACKAGED	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. HALL 03NOV2005		TE Connectivity					
		CHK C. CASH 03NOV2005							
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MODULAR PLUG ASSEMBLY, 8 POSITION, SOLID WIRE —					
		APVD C. CASH 03NOV2005							
		PRODUCT SPEC 108-1163							
		APPLICATION SPEC 114-6016							
MATERIAL —		FINISH —		SIZE A2	CAGE CODE 00779	DRAWING NO C=554720	RESTRICTED TO —		
				CUSTOMER DRAWING			SCALE 4:1	SHEET 1 of 1	REV S