




AMP WIRE RANGE	UL E13288 RECOGNIZED
22-16 AWG STRANDED	22-16 AWG STRANDED

SP LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

- 1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC MIL-T-7928
COMMERCIAL WIRE RANGE IS 22-16
- 2 TIN PLATE 0.00254[.000100] MIN THK
PER MIL-T-10727
- 3 SILVER PLATE 0.01270[.000500] MIN THK
PER QQ-S-365

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm ² [509-3,260] CIR MILS STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

SUPERSEDED BY 35610

3	2-31769-3
2	31769
FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN DK SCHRUM 29JUN94 CHK DA PATTERSON 08AUG94 APVD CH KULYNYCH 08AUG94 PRODUCT SPEC APPLICATION SPEC WEIGHT - CUSTOMER DRAWING	TE TE Connectivity	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH SEE TABLE	NAME TERMINAL, KNIFE DISCONNECT, BUDGET	
MATERIAL COPPER PER ASTM B-152 ANNEALED		SIZE A2 CAGE CODE 00779 DRAWING NO C-31769 SCALE 10:1	RESTRICTED TO - SHEET 1 OF 1 REV C1