

**EP1345ETTS-88.300M**
[Click part number to visit Part Number Details page](#)
**REGULATORY COMPLIANCE** (Data Sheet downloaded on Oct 28, 2017)
[Click badges to download compliance docs](#)

Regulatory Compliance standards are subject to updates by governing bodies. Click the badges to download the latest compliance docs for this part number directly from Ecliptek.

**ITEM DESCRIPTION**

Quartz Crystal Clock Oscillators XO (SPXO) LVCMOS (CMOS) 3.3Vdc 14 Pin DIP Metal Thru-Hole 88.300MHz  $\pm 50$ ppm -40°C to +85°C

**ELECTRICAL SPECIFICATIONS**

|                                   |                                                                                                                                                                                                                                        |
|-----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Nominal Frequency                 | 88.300MHz                                                                                                                                                                                                                              |
| Frequency Tolerance/Stability     | $\pm 50$ ppm Maximum (Inclusive of all conditions: Calibration Tolerance at 25°C, Frequency Stability over the Operating Temperature Range, Supply Voltage Change, Output Load Change, First Year Aging at 25°C, Shock, and Vibration) |
| Aging at 25°C                     | $\pm 5$ ppm/year Maximum                                                                                                                                                                                                               |
| Operating Temperature Range       | -40°C to +85°C                                                                                                                                                                                                                         |
| Supply Voltage                    | 3.3Vdc $\pm 10\%$                                                                                                                                                                                                                      |
| Input Current                     | 28mA Maximum (Unloaded)                                                                                                                                                                                                                |
| Output Voltage Logic High (Voh)   | Vdd-0.4Vdc Minimum (IOH = -8mA)                                                                                                                                                                                                        |
| Output Voltage Logic Low (Vol)    | 0.4Vdc Maximum (IOL = +8mA)                                                                                                                                                                                                            |
| Rise/Fall Time                    | 4nSec Maximum (Measured at 20% to 80% of waveform)                                                                                                                                                                                     |
| Duty Cycle                        | 50 $\pm 10\%$ (Measured at 50% of waveform)                                                                                                                                                                                            |
| Load Drive Capability             | 15pF Maximum                                                                                                                                                                                                                           |
| Output Logic Type                 | CMOS                                                                                                                                                                                                                                   |
| Pin 1 Connection                  | Tri-State (Disabled Output: High Impedance)                                                                                                                                                                                            |
| Pin 1 Input Voltage (Vih and Vil) | 70% of Vdd Minimum to enable output, 20% of Vdd Maximum to disable output, No Connect to enable output.                                                                                                                                |
| Disable Current                   | 16mA Maximum (Pin 1 = Ground)                                                                                                                                                                                                          |
| Standby Current                   | 20 $\mu$ A Maximum (Pin 1 = Ground)                                                                                                                                                                                                    |
| Peak to Peak Jitter (tPK)         | 100pSec Maximum, 60pSec Typical                                                                                                                                                                                                        |
| RMS Period Jitter (tRMS)          | 13pSec Maximum, 10pSec Typical                                                                                                                                                                                                         |
| Start Up Time                     | 10mSec Maximum                                                                                                                                                                                                                         |
| Storage Temperature Range         | -55°C to +125°C                                                                                                                                                                                                                        |

**ENVIRONMENTAL & MECHANICAL SPECIFICATIONS**

|                              |                                       |
|------------------------------|---------------------------------------|
| Fine Leak Test               | MIL-STD-883, Method 1014, Condition A |
| Gross Leak Test              | MIL-STD-883, Method 1014, Condition C |
| Lead Integrity               | MIL-STD-883, Method 2004              |
| Mechanical Shock             | MIL-STD-202, Method 213, Condition C  |
| Resistance to Soldering Heat | MIL-STD-202, Method 210               |
| Resistance to Solvents       | MIL-STD-202, Method 215               |
| Solderability                | MIL-STD-883, Method 2003              |
| Temperature Cycling          | MIL-STD-883, Method 1010              |
| Vibration                    | MIL-STD-883, Method 2007, Condition A |

EP1345ETTS-88.300M

 Click part number to visit  
Part Number Details page

MECHANICAL DIMENSIONS (all dimensions in millimeters)



| PIN | CONNECTION                 |
|-----|----------------------------|
| 1   | Tri-State (High Impedance) |
| 7   | Ground/Case Ground         |
| 8   | Output                     |
| 14  | Supply Voltage             |

| LINE | MARKING                                                                                    |
|------|--------------------------------------------------------------------------------------------|
| 1    | ECLIPTEK                                                                                   |
| 2    | EP13TS<br>EP13=Product Series                                                              |
| 3    | 88.300M                                                                                    |
| 4    | XXYZZ<br>XX=Ecliptek Manufacturing Code<br>Y=Last Digit of the Year<br>ZZ=Week of the Year |

EP1345ETTS-88.300M

[Click part number to visit Part Number Details page](#)

OUTPUT WAVEFORM & TIMING DIAGRAM



# EP1345ETTS-88.300M

[Click part number to visit Part Number Details page](#)

## Test Circuit for CMOS Output



Note 1: An external  $0.1\mu\text{F}$  low frequency tantalum bypass capacitor in parallel with a  $0.01\mu\text{F}$  high frequency ceramic bypass capacitor close to the package ground and  $V_{DD}$  pin is required.

Note 2: A low capacitance ( $<12\text{pF}$ ), 10X attenuation factor, high impedance ( $>10\text{Mohms}$ ), and high bandwidth ( $>300\text{MHz}$ ) passive probe is recommended.

Note 3: Capacitance value  $C_L$  includes sum of all probe and fixture capacitance.

EP1345ETTS-88.300M

[Click part number to visit Part Number Details page](#)

Recommended Solder Reflow Methods



High Temperature Solder Bath (Wave Solder)

|                                     |                                                                                                                                          |
|-------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| TS MAX to TL (Ramp-up Rate)         | 3°C/Second Maximum                                                                                                                       |
| Preheat                             |                                                                                                                                          |
| - Temperature Minimum (TS MIN)      | 150°C                                                                                                                                    |
| - Temperature Typical (TS TYP)      | 175°C                                                                                                                                    |
| - Temperature Maximum (TS MAX)      | 200°C                                                                                                                                    |
| - Time (ts MIN)                     | 60 - 180 Seconds                                                                                                                         |
| Ramp-up Rate (TL to TP)             | 3°C/Second Maximum                                                                                                                       |
| Time Maintained Above:              |                                                                                                                                          |
| - Temperature (TL)                  | 217°C                                                                                                                                    |
| - Time (tL)                         | 60 - 150 Seconds                                                                                                                         |
| Peak Temperature (TP)               | 260°C Maximum for 10 Seconds Maximum                                                                                                     |
| Target Peak Temperature (TP Target) | 250°C +0/-5°C                                                                                                                            |
| Time within 5°C of actual peak (tP) | 20 - 40 Seconds                                                                                                                          |
| Ramp-down Rate                      | 6°C/Second Maximum                                                                                                                       |
| Time 25°C to Peak Temperature (t)   | 8 Minutes Maximum                                                                                                                        |
| Moisture Sensitivity Level          | Level 1                                                                                                                                  |
| Additional Notes                    | Temperatures shown are applied to back of PCB board and device leads only. Do not use this method for product with the Gull Wing option. |

EP1345ETTS-88.300M

[Click part number to visit Part Number Details page](#)

Recommended Solder Reflow Methods



Low Temperature Infrared/Convection 185°C

|                                     |                                                                                                               |
|-------------------------------------|---------------------------------------------------------------------------------------------------------------|
| TS MAX to TL (Ramp-up Rate)         | 5°C/Second Maximum                                                                                            |
| Preheat                             |                                                                                                               |
| - Temperature Minimum (TS MIN)      | N/A                                                                                                           |
| - Temperature Typical (TS TYP)      | 150°C                                                                                                         |
| - Temperature Maximum (TS MAX)      | N/A                                                                                                           |
| - Time (ts MIN)                     | 60 - 120 Seconds                                                                                              |
| Ramp-up Rate (TL to TP)             | 5°C/Second Maximum                                                                                            |
| Time Maintained Above:              |                                                                                                               |
| - Temperature (TL)                  | 150°C                                                                                                         |
| - Time (tL)                         | 200 Seconds Maximum                                                                                           |
| Peak Temperature (TP)               | 185°C Maximum                                                                                                 |
| Target Peak Temperature (TP Target) | 185°C Maximum 2 Times                                                                                         |
| Time within 5°C of actual peak (tp) | 10 Seconds Maximum 2 Times                                                                                    |
| Ramp-down Rate                      | 5°C/Second Maximum                                                                                            |
| Time 25°C to Peak Temperature (t)   | N/A                                                                                                           |
| Moisture Sensitivity Level          | Level 1                                                                                                       |
| Additional Notes                    | Temperatures shown are applied to body of device. Use this method only for product with the Gull Wing option. |

EP1345ETTS-88.300M

[Click part number to visit Part Number Details page](#)

Recommended Solder Reflow Methods



Low Temperature Solder Bath (Wave Solder)

|                                     |                                                                                                                                          |
|-------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| Ts MAX to TL (Ramp-up Rate)         | 5°C/Second Maximum                                                                                                                       |
| Preheat                             |                                                                                                                                          |
| - Temperature Minimum (Ts MIN)      | N/A                                                                                                                                      |
| - Temperature Typical (Ts TYP)      | 150°C                                                                                                                                    |
| - Temperature Maximum (Ts MAX)      | N/A                                                                                                                                      |
| - Time (ts MIN)                     | 30 - 60 Seconds                                                                                                                          |
| Ramp-up Rate (TL to TP)             | 5°C/Second Maximum                                                                                                                       |
| Time Maintained Above:              |                                                                                                                                          |
| - Temperature (TL)                  | 150°C                                                                                                                                    |
| - Time (tL)                         | 200 Seconds Maximum                                                                                                                      |
| Peak Temperature (TP)               | 245°C Maximum                                                                                                                            |
| Target Peak Temperature (TP Target) | 245°C Maximum 1 Time / 235°C Maximum 2 Times                                                                                             |
| Time within 5°C of actual peak (tP) | 5 Seconds Maximum 1 Time / 15 Seconds Maximum 2 Times                                                                                    |
| Ramp-down Rate                      | 5°C/Second Maximum                                                                                                                       |
| Time 25°C to Peak Temperature (t)   | N/A                                                                                                                                      |
| Moisture Sensitivity Level          | Level 1                                                                                                                                  |
| Additional Notes                    | Temperatures shown are applied to back of PCB board and device leads only. Do not use this method for product with the Gull Wing option. |

Low Temperature Manual Soldering

185°C Maximum for 10 Seconds Maximum, 2 times Maximum. (Temperatures listed are applied to device leads only. This method can be utilized with both Gull Wing and Non-Gull Wing devices.)

High Temperature Manual Soldering

260°C Maximum for 5 Seconds Maximum, 2 times Maximum. (Temperatures listed are applied to device leads only. This method can be utilized with both Gull Wing and Non-Gull Wing devices.)