

**TABLE 1: HOW TO ORDER SERIES 80 CORDSETS FOR HIGH SPEED DATA**

**Sample Part Number**

801-024	B	F	P	A	C	M	P	Z	-72
Connector Series	Cable	Cable Jacket	Strain Relief	Connector End A P1	Connector End B P2	Shell Material / Finish	Protective Cover	Shell Pol. Pos.	OAL Length
<b>800-035</b> Series 800 Cordset, UNF Threaded Coupling, Hex Nut	<b>A</b> 100BASE-T Ethernet 4 Cond. UTP, OAL Shield 4 Pin Connector	<b>F</b> FEP Fluorocarbon Jacket, Translucent Blue	<b>P</b> Polyamide Overmold	<b>A</b> Plug, with Male Pin Contacts	<b>A</b> Plug, with Male Pin Contacts	<b>M</b> Aluminum / Electroless Nickel RoHS Compliant	<b>P</b> Metal Protective Covers Included	Polarizing position depends on the connector series.	Overall Length In Inches
<b>801-024</b> Series 801 Cordset, Double- Start Threaded Coupling	<b>B</b> 100BASE-T Ethernet Quad, OAL Shield, 4 Pin Connector	<b>P</b> Low Smoke/ Zero Halogen Polyurethane Jacket, Black	<b>B</b> Metal Backshell	<b>B</b> Plug, with Female Socket Contacts	<b>B</b> Plug, with Female Socket Contacts	<b>NF</b> Aluminum / Cadmium with Olive Drab Chromate	<b>N</b> No Covers Supplied	For Series 800 and 803:  <b>N</b> Normal <b>X</b> Pos. X <b>Y</b> Pos. Y <b>Z</b> Pos. Z	12 Inch Min.
<b>803-007</b> Series 803 Cordset, Push- Pull With Bayonet Lock Coupling	<b>C</b> 1000BASE-T Gigabit Ethernet 8 Cond. UTP, OAL Shield, 10 Pin Connector	<b>H</b> Heat-Shrink Boot, Low Smoke/ Zero Halogen	<b>C</b> Receptacle, with Male Pin Contacts	<b>C</b> Receptacle, with Male Pin Contacts	<b>D</b> Receptacle, with Female Socket Contacts	<b>ZN</b> Aluminum / Zinc- Nickel with Olive Drab Chromate			
<b>804-013</b> Series 804 Cordset, Quick- Disconnect Push- Pull	<b>D</b> IEEE 1394 Hi-Speed Quad 110 Ohm, 4 Pin Connector				<b>D</b> Receptacle, with Female Socket Contacts	<b>ZNU</b> Aluminum / Zinc-Nickel with Black Chromate		For Series 801 and 805:  <b>A</b> Normal <b>B</b> Pos. B <b>C</b> Pos. C <b>D</b> Pos. D	
<b>805-007</b> Series 805 Cordset, Tri- Start Threaded Coupling with Ratchet and Ground Spring	<b>E</b> USB 2.0, Two #22 Power, One STP #26				<b>N</b> No Connector (Single- Ended)	<b>MT</b> Aluminum / Nickel-PTFE RoHS Compliant			
	<b>F</b> Two STP, 100 Ohm, OAL Shield, 4 Pin Connector					<b>Z1</b> Stainless Steel / Passivated RoHS Compliant		For Series 804:  <b>Omit</b> for Single Master Key  <b>A</b> Normal <b>B</b> Pos. B <b>C</b> Pos. C <b>D</b> Pos. D	
	<b>G</b> Four STP, 100 Ohm, OAL Shield, 10 Pin Connector								

Dimensions in inches (millimeters) and are subject to change without notice.

© 2010 Glenair, Inc.

CAGE Code 06324

Printed in U.S.A.

**GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912**

[www.glenair.com](http://www.glenair.com)

**K-4**

01-JANUARY-2010

E-Mail: [sales@glenair.com](mailto:sales@glenair.com)