



13	12	11	10	9	8	7	6	5	4	3	2	1
MATERIAL NO.	ENGINEERING NO.	LENGTH			POLES	ELECTRICAL SPECS						
1300130149	1R3004A20F0601	6'0" +2.19 -0 (1.83M +55.6 -0)			3	600 VOLTS, 13 AMPS						
1300130315	1R4004A20A1201	12.00' +.75 -0 (304.8 +19.1 -0)			4	600 VOLTS, 10 AMPS						
1300130443	1R5004A20A1201	12.00' +.75 -0 (304.8 +19.1 -0)			5	600 VOLTS, 8 AMPS						



- NOTES:
1. MATERIAL: SEE TABLE
 2. FINISHES: SEE TABLE
 3. MATES WITH: MINI CHANGE CABLE
 4. ELECTRICAL SPECIFICATIONS: SEE CHART
 5. ASSEMBLY IS RoHS COMPLIANT

FACE VIEW-FEMALE INSERT				
1 WHITE 2 BLACK	1 GREEN/YELLOW 2 BLACK 3 WHITE	1 BLACK 2 WHITE 3 RED 4 GREEN/YELLOW	1 WHITE 2 RED 3 GREEN/YELLOW 4 ORANGE 5 BLACK	1 WHITE 2 RED 3 GREEN/YELLOW 4 ORANGE 5 BLACK 6 BLUE

5	1	LABEL	VINYL	BLACK/YELLOW
4	A/R	WIRE, 16 AWG, UL1015	PVC INSULATION	SEE WIRE DIAGRAM
3	A/R	CONTACT SOCKET	Cu ALLOY	GOLD PLATED
2	1	INSERT	PVC	YELLOW
1	1	RECEPTACLE SHELL	ST. STEEL	PASSIVATED
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

NEW SALES DWG.
EC NO: JG2013-0880
2013/01/11
DRAWN BY: DRWNRSTONE
2013/01/25
CHKD BY: JOZWIK
2013/03/01
APPR: JFMURPHY

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± ---
2 PLACES ± 0.05 ± .01
1 PLACE ± 0.10 ± ---
0 PLACE ± --- ± ---
ANGULAR ± .5 °
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE IN/MM
DRAWN BY: RSTONE
DATE: 2013/01/11
CHECKED BY: K. JOZWIK
DATE: 2013/01/25
APPROVED BY: JFMURPHY
DATE: 2013/03/01
MATERIAL NO. SEE CHART
SIZE C

SCALE 15:1
DESIGN UNITS INCH
THIRD ANGLE PROJECTION
TITLE MINI CHANGE FEM. RECEPT. EXT THD, 16 AWG 1/2 NPT MTG THD, SS
DOCUMENT NO. SD-130013-041
SHEET NO. 1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION