



All information is subject to change without notice

G065VN01 V2

(Preliminary)

G065VN01 V2

Color TFT-LCD Module

(HMI, FA, IPC, POS, KIOSK, Gaming, Medical.. etc.)

Features



- VGA resolution
- LED BLU driver built-in
- Long LED life time
- Wide dimming range support
- Replaceable LED light bar
- Wide operation temperature
- Reverse scan
- 6/8 bit convertible
- RoHS and Halogen-free compliance
- Min. 3 years product life support

Sample Schedule:

- * ES: 04/M' 2009
- * CS: 05/M' 2009
- * MP: 06/M' 2009

Specification

Size (inch)	6.5"
Model	G065VN01 V2
Resolution (pixel)	640RGB(H)x480(V)
Active Area (mm)	132.48(H) x 99.36(V)
Pixel Pitch (mm)	0.207 x 0.207
Mode	TN, Normal White
LCD Surface	AG
Number of Colors	262K/16.2M
View Angle (H/V)	160/140
Brightness(nit)	500
Contrast Ratio	800:1
Response Time (ms)	25
LED Life (hrs.)	50K
Power Consumption (W)	2.9 (max) All black pattern
LCD Supply Voltage (V)	3.3
Storage Temp. (°C)	-30 ~ +85
Operation Temp. (°C)	-30 ~ +85
Outline Dimension (mm)	153.0 x 121.0 x 10.9
Weight (g)	170
Interface	LVDS





All information is subject to change without notice

G065VN01 V2

(Preliminary)

CN1 pin assignment (LCD)

Connector: 20268-020E-12F (I-PEX or compatible)

Mating Connector: 20230-020B or 20230-T20-F or 20230-W20B-F (I-PEX or compatible)

Pin No.	Symbol	Pin Description
1	VDD	Power supply, 3.3V (typical)
2	VDD	Power supply, 3.3V (typical)
3	GND	Ground
4	GND	Ground
5	RxIN0-	Negative LVDS differential input(R0-R5, G0)
6	RxIN0+	Positive LVDS differential input(R0-R5, G0)
7	GND	Ground
8	RxIN1-	Negative LVDS differential input(G1-G5, B0-B1)
9	RxIN1+	Positive LVDS differential input(G1-G5, B0-B1)
10	GND	Ground
11	RxIN2-	Negative LVDS differential input(B2-B5, Hsync, Vsync, DE)
12	RxIN2+	Positive LVDS differential input(B2-B5, Hsync, Vsync, DE)
13	GND	Ground
14	RxCLKIN-	Negative LVDS differential clock input
15	RxCLKIN+	Positive LVDS differential clock input
16	SEL68	Selection for either 6bit or 8bit LVDS input: SEL68 = "High" or "NC", accepts 6bit LVDS data input; SEL68 = "Low", accepts 8bit LVDS data input.
17	U/D	Vertical Reverse ("L" or Open: Normal, "H": Reverse)
18	L/R	Horizontal Reverse ("L" or Open: Normal, "H": Reverse)
19	RxIN3-	Negative LVDS differential input (R6-R7, G6-G7, B6-B7) NC for 6bit LVDS input.
20	RxIN3+	Positive LVDS differential input (R6-R7, G6-G7, B6-B7) NC for 6bit LVDS input.


CN2 pin assignment (LED)

Connector: 53261-0671 (MOLEX or compatible)

Mating Connector: 51021-0600 (MOLEX or compatible)

Pin No.	Symbol	Pin Description
1	VLED	Power supply, +12V
2	VLED	Power supply, +12V
3	GND	Ground
4	GND	Ground
5	ON/OFF	"H (+3.3V)": ON, "L (GND or Open)": OFF
6	PWM	1-100% (200 Hz)

ALL RIGHTS STRICTLY RESERVED. ANY PORTION OF THIS PAPER SHALL NOT BE REPRODUCED, COPIED, OR TRANSFORMED TO ANY OTHER FORMS WITHOUT PERMISSION FROM AU OPTRONICS CORP.





Reliability specification

All information is subject to change without notice

G065VN01 V2

(Preliminary)

Items	Required Condition	Remark
Temperature Humidity Bias	40℃/90%,300Hr	Note 2
High Temperature Operation	85℃,300Hr	Note 2
Low Temperature Operation	-30℃,300Hr	Note 2
High Temperature Storage	85℃,300 hours	Note 2
Low Temperature Storage	-30℃,300 hours	Note 2
Thermal Shock Test	-20℃/30 min ,60℃/30 min ,100cycles	Note 2
Hot Start Test	85℃/1 Hr (min.), power on/off per 5 minutes, repeat 5 times	Note 2
Cold Start Test	-30℃/1 Hr (min.), power on/off per 5 minutes, repeat 5 times	Note 2
Shock Test (Non-Operating)	50G,20ms,Half-sine wave, (±X, ±Y, ±Z)	Note 2
Vibration Test (Non-Operating)	1.5G, 10~200~10Hz, Sine wave, 30mins/axis, 3 direction (X, Y, Z)	Note 2
ESD	Contact Discharge: ±8KV, 150pF(330Ω) 1sec, 8 points, 25 times/point Air Discharge: ±15KV, 150pF(330Ω) 1sec, 8 points, 25 times/point	Note 1,2
Attitude Test	Operating: 14,000 ft, Ramp: 2000 ft/min, 8hrs Non-operating: 40,000 ft, Ramp: 2000 ft/min, 24hrs	Note 2

Note1: According to EN61000-4-2 ESD class B criteria, some performance degradation is allowed. TFT-LCD module is self-recoverable, no data lost and no hardware failures after test.

Note2:

- Water condensation is not allowed for each test items.
- Each test is done by new TFT-LCD module. Don't use the same TFT-LCD module repeatedly for reliability test.
- The reliability test is performed only to examine the TFT-LCD module capability.
- To inspect TFT-LCD module after reliability test, please store it at room temperature and room humidity for 24 hours at least in advance.