


## Model 6251 Minigrabber® Test Clip To Straight Banana Plug Test Lead



### FEATURES:

- Newly designed Minigrabber® Test Clip Patch Cord offers a high 300 volt and 5 amperes rating.
- Grabber width is a slim .36" (9,14 mm) for easier side by side stacking.
- Grabber hook is gold plated Beryllium Copper to ensure signal integrity & attaches onto component leads up to .060" (1,5mm) O.D.
- Grabber patch cord interfaces directly into the most popular multimeters configured with non-sheathed style banana jacks, including Amprobe, Fluke, H-P, Tektronix and Wavetek.
- For added safety, the grabber body insulation material is fire retardant Nylon 6, UL94V-0 rated.
- Plug is molded directly to the cable in an integral one-piece design for a long lasting connection.
- Multi-leaf banana spring material is nickel plated Beryllium Copper for extended insertion life & low contact resistance.
- High strand count silicone insulated wire offers excellent flexibility and high temperature resistance.

### MATERIALS:

Grabber: Body: Nylon 6 – Fire Retardant – UL94 V-O Rated, Color per part number

Hook: Beryllium Copper, Gold Plated, Compression Spring: Music Wire

Wire: 18 AWG, 65 x 36 t.c., Insulation – Silicone, .144" (3,66 mm) O.D., Length: 12" (30,48 cm), Color per P/N.

Banana Plug: Body - Brass, Nickel Plated, Spring – Beryllium Copper, Nickel Plated

Insulation – Polypropylene, Color per part number

### RATINGS:

IEC 1010 2-031, Category II, P2 Compliant

Operating Voltage: 300 VRMS/DC Max.

Current: 5 Amperes Max.

### ORDERING INFORMATION: Model 6251-12-\*

\* = Color Code, -0 Black and -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[6251-12-0](#) [6251-12-2](#) [6251-24-2](#) [6251-24-0](#) [6251-36-2](#) [6251-36-0](#)