





GAGE DIMENSIONS APPLY WHEN TOOL IS
BOTTOMED BUT NOT UNDER PRESSURE.

FOR REPLACEMENT OF PARTS OTHER THAN
LISTED, TOOL SHOULD BE RETURNED TO OUR
FACTORY TO INSURE PROPER CERTI-CRIMP
ADJUSTMENT.



GAGE DIM.	
GO	NO GO
.119	.125

REVISION RECORD			
REVISED	BY	CHK	DATE
M	REVISED	MO	
L	REVISED	QT	MO 12-13
H	REVISED	B.S.	12-13
H	REVISED	B.S.	12-13
G	REVISED	CM	12-13
F	REVISED	CM	12-13
E	REVISED	R.Y.	12-13
D	REVISED	R.Y.	12-13
LTR	REVISION RECORD	DR	CHK

REQUIRED PER ASSEMBLY			
NUMBER	DESCRIPTION	NUMBER	DESCRIPTION
45329		45329	

4	A	313036-3	LABEL BLUE	9
1	A	305076	STOP	8
1	A	321016-4	SCREW	7
2	A	21045-6	RING - RETAINING	6
1	A	300449	PIN - RETAINING	5
1	A	39364	SPRING	4
1	A	39366	COLLAR	3
2	C	8-59558-0	PIN - RETAINING	2
4	A	21045-3	RING - RETAINING	1

DWG SIZE	NUMBER	NAME	REMARKS	ITEM NO.
©1959 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.				
CUSTOMER COPY REFERENCE ONLY				
MATERIAL AND FINISH		AMP INCORPORATED HARRISBURG PENNA.		
WIRE - RANGE - INSULATION		TYPE VS		
TOLERANCE EXCEPT AS NOTED		SCALE 1/2"		
NAME		LOC A B NO 45329		
HAND TOOL ASSEMBLY				