





PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM*A"
70230-X01/X01LF	1.6	2.90
70230-X11/X11LF	2.4	3.53



PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL




PRODUCT AFTER HOT RIVETTING.



NOTES:



- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
3 PLATING SOLDER TAILS 2-8 um SnPb 90-97 OR 2-8 um PURE Sn
4 INDICATED HOLES ARE UNPLATED.
5 PRODUCT MARKING: PART NUMBER & BATCH ID.
6 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
7 THE HOUSING WILL WITHSTAND EXPOSURE TO 260 DEGREE PEAK
TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER
APPLICATION.
8 DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE
BOTH SIDES OF PRODUCT.





RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 www.Falconconnect.com	
ltr ecn nld date				linear		  mm		title RA FEMALE SIGNAL STB 96 mm VERSION	
K	DG06-0064	Cdw	04/21/21					product family METRAL(tn)	
N	DG06-0477	CenH	11/20/069			scale 5:1		size	213
N	DG07-0168	CenH	05/10/07	angles		A2		70230	sheet 1 of 3
N	DG09-0068	CenH	06/06/09	dr R-ridge	900919				
				engrh. Bouwmeijer	940308				
H	V00579	LLA	000316	chrp A van Zanten	900919				
J	V00847	LLA	000530	opdr. van Voensel	900919				
sheet revision				N N N					
index sheet				1 2 3					

PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM"A"
70230-X02/X02LF	1.6	2.90
70230-X12/X12LF	2.4	3.53




PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL



NOTES:

- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
- 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 PLATING SOLDER TAILS 2-8 鍍 SnPb 90-97 OR 2-8 鍍 PURE Sn
- 4 INDICATED HOLES ARE UNPLATED.
- 5 PRODUCT MARKING: PART NUMBER & BATCH ID.
- 6 SET BACK FOR PRESS BLOCK.
- 7 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD
- 8 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 9 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
- 10 DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.

14.64 REF. SEE NOTE 6




RECOMMENDED HOLE PATTERN, COMPONENT SIDE.

nat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
litr	ecnr	nodr	date	linear	projection	title	www.fciconnection
N						RA FEMALE SIGNAL	
				angles		STB 96 mm VERSION	
				dir	D. de Bil	970529	
				engr	P. Schalk	970529	
				chr	P. Schalk	970529	
				app	H. Coolmans	970529	
sheet	revision			scale	5:1	product family METAL (tm)	code
index	sheet					sizedwg no	213
						A2	70230
							sheet
							2 of-




All rights strictly reserved. Reproduction or issue in any form without written authority from the proprietor.
Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite du propriétaire.
Property of FCI S.A.
© FCI S.A.


PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM"A"
70230-X03/X03LF	1.6	2.90
70230-X13/X13LF	2.4	3.53




NOTE 11



PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL




PRODUCT AFTER HOT RIVETTING.



NOTES:

- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
- 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 PLATING SOLDER TAILS 2-8 鍍 SnPb 90-97 OR 2-8 鍍 PURE Sn
- 4 INDICATED HOLES ARE UNPLATED.
- 5 PRODUCT MARKING: PART NUMBER & BATCH ID.
- 6 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 7 THE HOUSING WILL WITHSTAND EXPOSURE TO 260 DEGREE PEAK
TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER
APPLICATION.
- 8 DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE
BOTH SIDES OF PRODUCT.



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

nat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
litr	ecn	nodr	date	linear	projection	title	www.fciconnection
N						RA FEMALE SIGNAL STB 96 mm VERSION	
				angles	mm	product family	code
				dir	Heaven Cen	11/20/06	213
				engr	Collins Lu	11/20/06	
				chr	Beer Fu	11/20/06	
				appd	Joseph Hsia	11/20/06	
sheet	revision			scale	5:1	A2	70230
index	sheet						3 of 3