





CIRCUIT: SPDT
CONTACT CONFIGURATION

SWITCH FUNCTION	
PDS 1	PDS 2
↗	⇒
DN	DN



LEGEND

- =OFF POSITION
- =INDICATES KEY PULL
- ⌘ =INDICATES NO KEY PULL

- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 3. TERM. NOS. FDR REFERENCE ONLY.
 4. RATING: 2A @125VAC, 1A @250VAC
 5. CONTACT RESISTANCE: 10mILLI-OHMS max.
 6. DIELECTRIC STRENGTH: 1000 VAC-1Minute
 7. INSULATION RESISTANCE: 200Mega OHMS min.
 8. MATERIALS:

HOUSING: ZINC ALLOY DIE CAST, SATINE CHROME PLATING
CYLINDER: ZINC ALLOY W/SATIN CHROME PLATING
TERMINAL AND CONTACTS: SILVER PLATED
KEYS (2) KEY CODE 10001:
TUBULAR STEEL, NICKLE PLATING

TITLE				E-SWITCH®			
A	11737	RELEASED FOR PRODUCTION	10/12/01	CJB	K0124C-10001		
REV.	ECN No.	DESCRIPTION	DATE	CHKD			
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE	DATE	DR
					1.5:1	10/12/01	CJB
							DWG
							K500105
							REV
							A