

## LM160/LM360 High Speed Differential Comparator

Check for Samples: [LM160](#), [LM360](#)

### FEATURES


- Ensured high speed: 20 ns max
- Tight delay matching on both outputs
- Complementary TTL outputs
- High input impedance
- Low speed variation with overdrive variation
- Fan-out of 4
- Low input offset voltage
- Series 74 TTL compatible

### DESCRIPTION


The LM160/LM360 is a very high speed differential input, complementary TTL output voltage comparator with improved characteristics over the  $\mu$ A760/ $\mu$ A760C, for which it is a pin-for-pin replacement. The device has been optimized for greater speed, input impedance and fan-out, and lower input offset voltage. Typically delay varies only 3 ns for overdrive variations of 5 mV to 400 mV.

Complementary outputs having minimum skew are provided. Applications involve high speed analog to digital convertors and zero-crossing detectors in disk file systems.

### CONNECTION DIAGRAMS



**Figure 1. Package Number LMC0008C** <sup>(1)</sup>



**Figure 2. Package Number D0008A or P0008E**

(1) Also available in SMD# 5962-8767401



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

All trademarks are the property of their respective owners.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of the Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

Copyright © 1999–2013, Texas Instruments Incorporated

**Absolute Maximum Ratings** <sup>(1)</sup> <sup>(2)</sup>

|                                                                                                                                     |                          |                            |
|-------------------------------------------------------------------------------------------------------------------------------------|--------------------------|----------------------------|
| Positive Supply Voltage                                                                                                             |                          | +8V                        |
| Negative Supply Voltage                                                                                                             |                          | –8V                        |
| Peak Output Current                                                                                                                 |                          | 20 mA                      |
| Differential Input Voltage                                                                                                          |                          | ±5V                        |
| Input Voltage                                                                                                                       |                          | $V^+ \geq V_{IN} \geq V^-$ |
| ESD Tolerance <sup>(3)</sup>                                                                                                        |                          | 1600V                      |
| Operating Temperature Range                                                                                                         | LM160                    | –55°C to +125°C            |
|                                                                                                                                     | LM360                    | 0°C to +70°C               |
| Storage Temperature Range                                                                                                           |                          | –65°C to +150°C            |
| Lead Temperature                                                                                                                    | (Soldering, 10 sec.)     | 260°C                      |
| Soldering Information                                                                                                               |                          |                            |
| PDIP Package                                                                                                                        | Soldering (10 seconds)   | 260°C                      |
| SOIC Package                                                                                                                        | Vapor Phase (60 seconds) | 215°C                      |
|                                                                                                                                     | Infrared (15 seconds)    | 220°C                      |
| See AN-450 “Surface Mounting Methods and Their Effect on Product Reliability” for other methods of soldering surface mount devices. |                          |                            |

- (1) The device may be damaged if used beyond the maximum ratings.  
 (2) Refer to RETS 160X for LM160H, LM160J-14 and LM160J military specifications.  
 (3) Human body model, 1.5 kΩ in series with 100 pF.







## Electrical Characteristics

 $(T_{MIN} \leq T_A \leq T_{MAX})$ 

| Parameter                                                       | Conditions                                | Min     | Typ       | Max  | Units            |
|-----------------------------------------------------------------|-------------------------------------------|---------|-----------|------|------------------|
| Operating Conditions                                            |                                           |         |           |      |                  |
| Supply Voltage $V_{CC}^+$                                       |                                           | 4.5     | 5         | 6.5  | V                |
| Supply Voltage $V_{CC}^-$                                       |                                           | -4.5    | -5        | -6.5 | V                |
| Input Offset Voltage                                            | $R_S \leq 200\Omega$                      |         | 2         | 5    | mV               |
| Input Offset Current                                            |                                           |         | 0.5       | 3    | $\mu A$          |
| Input Bias Current                                              |                                           |         | 5         | 20   | $\mu A$          |
| Output Resistance (Either Output)                               | $V_{OUT} = V_{OH}$                        |         | 100       |      | $\Omega$         |
| Response Time                                                   | $T_A = 25^\circ C, V_S = \pm 5V^{(1)(2)}$ |         | 13        | 25   | ns               |
|                                                                 | $T_A = 25^\circ C, V_S = \pm 5V^{(3)(2)}$ |         | 12        | 20   | ns               |
|                                                                 | $T_A = 25^\circ C, V_S = \pm 5V^{(4)(2)}$ |         | 14        |      | ns               |
| Response Time Difference between Outputs                        |                                           |         |           |      |                  |
| $(t_{pd} \text{ of } +V_{IN1}) - (t_{pd} \text{ of } -V_{IN2})$ | $T_A = 25^\circ C^{(1)(2)}$               |         | 2         |      | ns               |
| $(t_{pd} \text{ of } +V_{IN2}) - (t_{pd} \text{ of } -V_{IN1})$ | $T_A = 25^\circ C^{(1)(2)}$               |         | 2         |      | ns               |
| $(t_{pd} \text{ of } +V_{IN1}) - (t_{pd} \text{ of } +V_{IN2})$ | $T_A = 25^\circ C^{(1)(2)}$               |         | 2         |      | ns               |
| $(t_{pd} \text{ of } -V_{IN1}) - (t_{pd} \text{ of } -V_{IN2})$ | $T_A = 25^\circ C^{(1)(2)}$               |         | 2         |      | ns               |
| Input Resistance                                                | $f = 1 \text{ MHz}$                       |         | 17        |      | k $\Omega$       |
| Input Capacitance                                               | $f = 1 \text{ MHz}$                       |         | 3         |      | pF               |
| Average Temperature Coefficient of Input Offset Voltage         | $R_S = 50\Omega$                          |         | 8         |      | $\mu V/^\circ C$ |
| Average Temperature Coefficient of Input Offset Current         |                                           |         | 7         |      | nA/ $^\circ C$   |
| Common Mode Input Voltage Range                                 | $V_S = \pm 6.5V$                          | $\pm 4$ | $\pm 4.5$ |      | V                |
| Differential Input Voltage Range                                |                                           | $\pm 5$ |           |      | V                |
| Output High Voltage (Either Output)                             | $I_{OUT} = -320 \mu A, V_S = \pm 4.5V$    | 2.4     | 3         |      | V                |
| Output Low Voltage (Either Output)                              | $I_{SINK} = 6.4 \text{ mA}$               |         | 0.25      | 0.4  | V                |
| Positive Supply Current                                         | $V_S = \pm 6.5V$                          |         | 18        | 32   | mA               |
| Negative Supply Current                                         | $V_S = \pm 6.5V$                          |         | -9        | -16  | mA               |


- (1) Response time measured from the 50% point of a 30 mVp-p 10 MHz sinusoidal input to the 50% point of the output.
- (2) Measurements are made in AC Test Circuit, Fanout = 1
- (3) Response time measured from the 50% point of a 2 Vp-p 10 MHz sinusoidal input to the 50% point of the output.
- (4) Response time measured from the start of a 100 mV input step with 5 mV overdrive to the time when the output crosses the logic threshold.


## Typical Performance Characteristics



## Typical Performance Characteristics (continued)


### Common-Mode Pulse Response



**AC TEST CIRCUIT**

|                              |                     |                     |
|------------------------------|---------------------|---------------------|
| $V_{IN} = \pm 50 \text{ mV}$ | FANOUT=1            | FANOUT=4            |
| $V^+ = +5\text{V}$           | $R = 2.4\text{k}$   | $R = 630\Omega$     |
| $V^- = -5\text{V}$           | $C = 15 \text{ pF}$ | $C = 30 \text{ pF}$ |

# SCHEMATIC DIAGRAM



## REVISION HISTORY

### Changes from Revision B (March 2013) to Revision C

### Page

- Changed layout of National Data Sheet to TI format ..... [7](#)

## PACKAGING INFORMATION

| Orderable part number | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-----------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| LM360M                | Obsolete      | Production           | SOIC (D)   8   | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | LM<br>360M          |
| LM360M/NOPB           | Active        | Production           | SOIC (D)   8   | 95   TUBE             | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | LM<br>360M          |
| LM360M/NOPB.B         | Active        | Production           | SOIC (D)   8   | 95   TUBE             | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | LM<br>360M          |
| LM360MX               | Obsolete      | Production           | SOIC (D)   8   | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | LM<br>360M          |
| LM360MX/NOPB          | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | LM<br>360M          |
| LM360MX/NOPB.B        | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | LM<br>360M          |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LM360MX/NOPB | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.5     | 5.4     | 2.0     | 8.0     | 12.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LM360MX/NOPB | SOIC         | D               | 8    | 2500 | 367.0       | 367.0      | 35.0        |

## TUBE



\*All dimensions are nominal

| Device        | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|---------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| LM360M/NOPB   | D            | SOIC         | 8    | 95  | 495    | 8      | 4064   | 3.05   |
| LM360M/NOPB.B | D            | SOIC         | 8    | 95  | 495    | 8      | 4064   | 3.05   |



## PACKAGE OUTLINE

**SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT





1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
4. This dimension does not include interlead flash.
5. Reference JEDEC registration MS-012, variation AA.

# EXAMPLE BOARD LAYOUT

D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



4214825/C 02/2019

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON .005 INCH [0.125 MM] THICK STENCIL  
SCALE:8X

4214825/C 02/2019

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2025, Texas Instruments Incorporated