


THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.


Rating	8A 125V AC, 4A 250V AC			Mounting Hole		Circuit Diagram											
	10A 125V AC, 6A 250V AC							C  US									
	10A 28V DC, 6A 14 VT																
	6A 250V ~  16 																
Contact Resistance	50m ohm max.			<table><tr><td>Thickness</td><td>X</td><td>Y</td></tr><tr><td>0.75 - 1.25</td><td>19.2 - 0.1</td><td>7.0 + 0.1</td></tr><tr><td>1.25 - 2.00</td><td>19.4 - 0.1</td><td>7.0 + 0.1</td></tr><tr><td>2.00 - 3.00</td><td>19.8 - 0.1</td><td>7.0 + 0.1</td></tr></table>	Thickness	X	Y	0.75 - 1.25	19.2 - 0.1	7.0 + 0.1	1.25 - 2.00	19.4 - 0.1	7.0 + 0.1	2.00 - 3.00	19.8 - 0.1	7.0 + 0.1	SPST (ON) - OFF () = Momentary
Thickness	X	Y															
0.75 - 1.25	19.2 - 0.1	7.0 + 0.1															
1.25 - 2.00	19.4 - 0.1	7.0 + 0.1															
2.00 - 3.00	19.8 - 0.1	7.0 + 0.1															
Insulation Resistance	DC 500V 100M ohm min.																
Dielectric Strength	AC 1500V 1 minute																
Operating Temperature	-25 °C ~ 85 °C																
Switch Function	2P SPST (ON)-OFF																

Material:

Frame: Nylon#66, Black

Actuator: Nylon#66, Black

Printed: None



RoHS Compliant

1 Updated drawing. Rotated button to opposite direction. 7/22/10

CW INDUSTRIES
 Southampton, Pa. 18966
 Tel 215.355.7080/www.cwind.com

Date Drawn: 12/21/09

Rev. 1

Unit: mm

Checked By: G.GULD

Title:

ROCKER SWITCH

CW P/N:

GRB243F02BB