

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

JAN , 2005.

© COPYRIGHT 2005 By -

ALL RIGHTS RESERVED.

LOC

	DIST
--	------

REVISIONS

	F
--	---

LTR

DESCRIPTION

DATE _____

DWN

APVD

B1

REVISÉD PER ECO-11-005033

01APR11

RK

HMR


	C
--	---

ECO-12-014680

20Aug201



2	TITAN
---	-------

MARTIN




NOTES


- ① 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
 - ② SINGLE PACK IN ACCORDANCE WITH AMP SPEC 107-3275
 - ③ Au PLATING OVER Ni PLATING OVER Cu PLATING
 - ④ Ni PLATING OVER Cu PLATING
5. FOR TECHNICAL DATA REFER TO YOUR LOCAL TE CONNECTIVITY SALES OFFICE
 6. ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



RECOMMENDED
PANEL CUTOUT
DIMENSIONS



				Obsolete	Obsolete		Obsolete				
				1	1	1	1	BRASS	<u>4</u>	HEX NUT	7
				1	1	1	1	BRASS	<u>4</u>	SOLDER TAG	6
				1	1	1	1	STEEL	<u>4</u>	LOCK WASHER	5
				1	1	1	1	PHOS BRONZE	<u>3</u>	CONTACT	4
				1	1	—	—	POLYMETHYLPENTENE		INSULATOR	3
				—	—	1	1	POLYMETHYLPENTENE		INSULATOR	2
				1	1	—	—	ZINC ALLOY	<u>4</u>	BODY	1
				5--3	5--2	5--1	5--0	MATERIAL		DESCRIPTION	ITEM
				<u>2</u>	<u>1</u>	<u>2</u>	<u>1</u>				
QUANTITY PER ASSY								PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RITA ZUO 14 Feb 09		 TE Connectivity	
DIMENSIONS: mm		CHK ANSON MA 14 Feb 09		NAME BNC BULKHEAD SOCKET FRONT MOUNT WITH SOLDER TAG —	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD BOB ZHAO 14 Feb 09			
		PRODUCT SPEC 108-112000			
0 PLC ± 0.5 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± — 4 PLC ± — ANGLES ± —		APPLICATION SPEC —			
MATERIAL SEE TABLE		FINISH —		SIZE A3	
		WEIGHT —		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-1634523	
				RESTRICTED TO —	
				SCALE NTS	
				SHEET 1 OF 1	
				REV C	