


© COPYRIGHT 1998 BY SPC TECHNOLOGY. ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.


REVISIONS				DOC. NO. SPC-F005, Total Pages: 2			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD
129	A	RELEASED	DJC	7/6/98	JC	7/6/98	JMM
							7/7/98



SPECIFICATIONS:

IMPEDANCE: 50 OHMS
VOLTAGE RATING: 335 VRMS @ SEA LEVEL
FREQUENCY RANGE: 0-2.5 GHz
INSERTION LOSS: ≤ -2 dB @ 2 GHz
VSWR MAX: 1.25:1 @ 2 GHz
FOR RG-58, 58A, 58C, 141, 141A, 400/U, BELDEN 8219,
8240, 8259, 8262, 9201, 9203, 9310, 9311,
COMM/SCOPE 0268 & CUSHCRAFT ULTRALINK TL92463E

5	SHELL	1	BRASS	NICKEL
4	FERRULE	1	COPPER TUBING	NICKEL
3	DIELECTRIC	1	DELRI	NONE
2	CONTACT	1	BRASS	GOLD
1	BODY	1	BRASS	NICKEL
ITEM	DESCRIPTION	QTY	MATERIAL	FINISH



SUGGESTED CRIMP DIES: .052 & .213

SUGGESTED STRIPPING INSTRUCTIONS

DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



UNLESS OTHERWISE

SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:	DATE:
DANIEL CAREY	7/6/98
CHECKED BY:	DATE:
JOHN COLE	7/6/98
APPROVED BY:	DATE:
JEFF MCVICKER	7/7/98

DRAWING TITLE:

MINI UHF MALE CRIMP

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	1507	92N3353.DWG	A
SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1