




GBPC 40, 50 SERIES

High Current 40, 50 AMPS. Single Phase
Glass Passivated Bridge Rectifiers


Features

- ✧ UL Recognized File # E-326243
- ✧ Glass passivated junction
- ✧ The plastic material used carries Underwriters Laboratory Flammability Recognition 94V-0
- ✧ Integrally molded heatsink provide very low thermal resistance for maximum heat dissipation
- ✧ Universal 4-way terminals; snap-on, wrap-around, solder or P.C. board mounting
- ✧ Surge overload ratings 400 amperes
- ✧ Typical I_R less than 0.2 μ A
- ✧ High temperature soldering guaranteed: 260°C / 10 seconds / .375", (9.5mm) lead lengths
- ✧ Isolated voltage from case to lead over 2500 volts

GBPC40



GBPC40 -M



Mechanical Data

Dimensions in inches and (millimeters)

- ✧ Case: Molded plastic body.
- ✧ Terminals: Pure tin plated, Lead free. leads solderable per MIL-STD-202, Method 208 .
- ✧ Weight: 17.37 grams
- ✧ Mounting position: Any
- ✧ Mounting Torque: 20 inches-lbs. max.

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	-005	-01	-02	-04	-06	-08	-10	Units
Maximum Recurrent Peak Reverse Voltage	VRRM	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	VRMS	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	VDC	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current @T _C = 55 °C GBPC40 GBPC50	I _{F(AV)}	40.0 50.0							A
Peak Forward Surge Current, Single Sine-wave Superimposed on Rated Load GBPC40 (JEDEC method) GBPC50	I _{FSM}	400 400							A
Maximum Instantaneous Forward Voltage Drop Per Element at Specified Current GBPC40 @20A GBPC50 @25A	V _F	1.1							V
Maximum DC Reverse Current at Rated DC Blocking Voltage Per Element (Note 1)	I _R	10							μ A
Typical Thermal Resistance	R _{θJC}	1.5							°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-50 to +150							°C

Notes: 1. Pulse Test with PW=300 usec, 1% Duty Cycle
2. Suffix "M" - Terminal Location Face to Face.

Version: C10

RATINGS AND CHARACTERISTIC CURVES (GBPC40005 THRU GBPC4010
GBPC50005 THRU GBPC5010)

FIG.1- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.2- TYPICAL REVERSE CHARACTERISTICS PER BRIDGE ELEMENT




FIG.3- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.4- TYPICAL FORWARD CHARACTERISTICS PER BRIDGE ELEMENT




FIG.5- TYPICAL JUNCTION CAPACITANCE

