




This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

MARKETING SALES DRAWING DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING DIMENSIONS IN METRIC - []



ORIENTATION

Electrical Testing
 per Tusonix standard
 test plans and Mil-Std-202
 Test Methods.



NOTES:

1. TUSONIX STANDARD P/N: 7608-501N,
 TUSONIX RoHS COMPLIANT P/N 7608-501NLF.
 CUSTOMER MUST SPECIFY STANDARD OR RoHS P/N WHEN ORDERING.
2. LEAD FINISH: MATTE TIN.
3. PLATE MATERIAL: .040" [1.02] COPPER ALLOY,
 MATTE TIN FINISH.
4. PART MARKING: TRADEMARK, PART NUMBER,
 DATE CODE, AND UL RECOGNITION: WHITE INK.
 RoHS PART: GREEN INK DOT.
5. MAX. SOLDERING TEMPERATURE 500°F [260°C].
6. BLOCK MOUNTING: RECOMMENDED MOUNTING SCREWS
 (# 8 PAN HEAD). TORQUE 4.5-5.5 in. lbs. [0.51-0.62 Nm].
7. MOLDED MATERIAL: HIGH TEMPERATURE THERMOPLASTIC
 (PBT), UL RATED 94 V-O.
8. U.L. FILE NO. E201344.

Cx (pF)	WVAC -40°C TO +125°C	I _{DC}	I.R. MIN. @ 100 (VDC.)	DWV (VAC)	TYPICAL NO LOAD INSERTION LOSS (dB) @ 25°C PER MIL-STD-220			
					10 MHz	100 MHz	1 GHz	10 GHz
2000 MIN.	250	20 Amps	10 G Ω	1500	5	50	60	65

X-2015 Rev-0	REVISION RECORD		A		TOLERANCES unless otherwise specified		Title FILTERED TERMINAL BLOCK 8 POSITION, UL RECOGNIZED		
	Original Release C.O. ECO-658				2 PLC. DECIMAL ± N/A				
					3 PLC. DECIMAL ± .030 [0.76]				
					ANGLES ± N/A		Drawn L.E. 04-14-09		Scale FULL
					TUSONIX TUCSON, ARIZONA		Approved R.L. 04-14-09		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[7608-501NLF](#)