


1757820-7 Product Details

Share

Print

Email



1757820-7

TE Internal Number: 1757820-7

Active

View 3D PDF

Subminiature D Pins/Sockets for MIL-C-24308 and MIL-C-39029

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Product Series = 109
- Connector Style = Receptacle
- Contact Type = Socket
- Density = Standard

View all Features

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List

Request Sample

Find Similar Products

Buy Product

Documentation & Additional Information	
Product Drawings: - AMPLIMITE RECEPTACLE ASSY,SIZE 1 THRU 5 SERIES 109 W... (PDF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: (CAD Format & Compression Information) 2D Drawing (DXF, Version H) 3D Model (IGES, Version H) 3D Model (STEP, Version H) List all Documents	Additional Information: - Product Line Information Additional Product Images: - Insert Arrangement Related Products: - Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Product Type = Connector - Product Series = 109 - Shell Size = 2 - Shell Material = Steel - Termination Method to Wire/Cable = Crimp - Mounting Hole Diameter (mm [in]) = 3.05 [.120] Body Features: - Number of Positions = 15 - Blindmate = No - Non-Magnetic = No - Rear Grommet = No - Power/Signal/Coax Combination = No - Shell Plating = Zinc - Mount Style = Mounting Holes - Retention Clip Material = Stainless Steel Contact Features: - Contact Type = Socket - Contact Size = 20 - Contact Style = Crimp Snap-in	Housing Features: - Connector Style = Receptacle Configuration Features: - Density = Standard Industry Standards: - Government/Industry Qualification = Yes - Government/Industry Part Number = M24308/2-2 - RoHS/ELV Compliance = RoHS compliant, ELV compliant - Lead Free Solder Processes = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C - RoHS/ELV Compliance History = Always was RoHS compliant - NASA Qualification = No Conditions for Usage: - Applies To = Wire/Cable Other: - Brand = AMP - Comment = Size 20 contacts supplied with connectors are loose piece.