

SPECIFICATIONS

Mechanical

Contact Retention Force: 0.10kg min.
Durability : 25 Cycles

Electrical

Voltage Rating: 25V
Current Rating: 0.3A
Contact Resistance: 50mW max.
Dielectric Withstanding Voltage: 250V AC/1 min.
Insulation Resistance: 100MW


Physical

Housing: Thermoplastic, UL 94V-0 rated in Ivory Color
Contact: Copper alloy
Plating: See "ORDERING INFORMATION"
Metal Spring: Copper alloy
Operating Temperature: -40 to +85


DDR II SO DIMM Socket

AS Series

5.2mm Height SMT Type
 0.60mm [.024"] Pitch
 200 Pos.



DRAWING



ORDERING INFORMATION

PRODUCT NO.: A S 0 A4 2 6 - N 2 * N - * F

Memory Module Socket — A
 Horizontal Type — S
 Single Row — 0
 No. of Pos. — A4
 SMT Type — 2
 Contact Area Plating — 6
 6=10u" Gold

— N
 — 2
 — *
 — N
 — *
 — F

F=Lead Free
 1=Hard Tray
 4=Soft Tray
 7=Tape Reel
 N=Normal Type
 S=Standard Type
 R=Reverse Type
 2=5.2mm Height
 N=DDR II SO DIMM (Type II)

ASDA426-N2RN-*F	11.40 [.449]	1.80 [.071]	2.40 [.094]
ASDA426-N2SN-*F	47.40 [1.866]	2.70 [.108]	1.50 [.059]
P/N	DIM. D	DIM. E	DIM. F
ASDA426-N2RN-*F	47.40 [1.866]	1.50 [.059]	2.70 [.108]
ASDA426-N2SN-*F	11.40 [.449]	2.40 [.094]	1.80 [.071]
P/N	DIM. A	DIM. B	DIM. C