







- | | |
|---|---|
| 1 | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND |
| 2 | 0.00254[.000100]—0.00508[.000200] MATTE TIN—LEAD OVER
0.00127[.000050] NICKEL ENTIRE POST. |
| 3 | HOUSING: LCP, COLOR—BLACK.
POSTS: PHOSPHOR BRONZE. |
| 4 | 0.00254[.000100]—0.00508[.000200] MATTE TIN OVER
0.00127[.000050] NICKEL ENTIRE POST. |
| 5 | PRELIMINARY PART — NOT RELEASED FOR PRODUCTION. |
| 6 | OBsolete PARTS: OBsolete CIS STREAMLINING PER D.RENAUD/D.SINISI |

OBSOLETE		35.56 [1.400]	14	35.69 [1.484]	15	6-146133-3	
		33.02 [1.300]	13	33.15 [1.384]	14	6-146133-2	
		30.48 [1.200]	12	30.61 [1.284]	13	6-146133-1	
		27.94 [1.100]	11	28.07 [1.184]	12	6-146133-0	
		25.40 [1.000]	10	27.53 [1.084]	11	5-146133-9	
		22.86 [.900]	9	24.99 [.984]	10	5-146133-8	
		20.32 [.800]	8	22.45 [.884]	9	5-146133-7	
OBSOLETE		17.78 [.700]	7	19.91 [.784]	8	5-146133-6	
		15.24 [.600]	6	17.37 [.684]	7	5-146133-5	
OBSOLETE		12.70 [.500]	5	14.83 [.584]	6	5-146133-4	
		10.16 [.400]	4	12.29 [.484]	5	5-146133-3	
		7.62 [.300]	3	9.75 [.384]	4	5-146133-2	
		5.08 [.200]	2	7.21 [.284]	3	5-146133-1	
		17.78 [.700]	7	19.91 [.784]	8	1-146133-5	
OBSOLETE 		35.56 [1.400]	14	35.69 [1.484]	15	1-146133-3	
		33.02 [1.300]	13	33.15 [1.384]	14	1-146133-2	
		30.48 [1.200]	12	30.61 [1.284]	13	1-146133-1	
		27.94 [1.100]	11	28.07 [1.184]	12	1-146133-0	
		25.40 [1.000]	10	27.53 [1.084]	11	146133-9	
		22.86 [.900]	9	24.99 [.984]	10	146133-8	
OBSOLETE 		20.32 [.800]	8	22.45 [.884]	9	146133-7	
		17.78 [.700]	7	19.91 [.784]	8	146133-6	
	OBSOLETE		15.24 [.600]	6	17.37 [.684]	7	146133-5
			12.70 [.500]	5	14.83 [.584]	6	146133-4
			10.16 [.400]	4	12.29 [.484]	5	146133-3
			7.62 [.300]	3	9.75 [.384]	4	146133-2
			5.08 [.200]	2	7.21 [.284]	3	146133-1
	PLATING	C	B	A	NO. OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J KNAUB 30SEP84 CHK G DUBNICZKI 30SEP84		Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC 1 PLC ± 2 PLC ± 3 PLC ± .127[.005] 4 PLC ± ANGLES ± ±		NAME SURFACE MOUNT HEADER ASSEMBLY, MOD II, BREAKAWAY, VERTICAL, SINGLE ROW, .100 X.100 C/L, .025 SQ. POST	
		PRODUCT SPEC — APPLICATION SPEC —		SIZE A1	
MATERIAL —		WEIGHT —		CAGE CODE 00775	
SEE TABLE 3		CUSTOMER DRAWING		DRAWING NO C-146133	
				RESTRICTED TO —	
				SCALE 1:1 SHEET 1 OF 1 REV 1	