

Customer Information Sheet

DRAWING No.: S7251-45R

IF IN DOUBT - ASK


©

NOT TO SCALE




THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm






- NOTES:
1. QUANTITY PER REEL = 8,000.
 2. THIS PRODUCT IS TAPED AND REELED IN GENERAL ACCORDANCE WITH EIA-481-2 (ELECTRONICS INDUSTRIES ASSOCIATION).



RECOMMENDED PCB LAYOUT
(TOLERANCE = ± 0.05)





COMPONENT DETAILS




SECTION Y-Y

SPECIFICATION:
MATERIAL = TITANIUM COPPER ALLOY, 0.08mm THICK
FINISH = 1.5 μ -3.5 μ NICKEL ALL OVER. 0.1 μ GOLD ON TOP
CONTACT AREA AND GOLD FLASH ON BASE
ELECTRICAL:
CONTACT RESISTANCE = 50m Ω MAX
CURRENT RATING = 1A
VOLTAGE RATING = 250V AC
MECHANICAL:
DURABILITY = 10,000 CYCLES
RECOMMENDED WORKING HEIGHT = 1.20mm / MIN FORCE = 0.58N
RECOMMENDED MINIMUM WORKING HEIGHT = 0.90mm
ENVIRONMENTAL:
OPERATING TEMPERATURE = -40°C TO +85°C



REEL DETAILS



FINISHED REELING DIRECTION

MSP	2	30.11.15	13179
NAME	ISS.	DATE	C/NOTE
APPROVED: M.PERREN			
CHECKED: S.BENNETT			
DRAWN: S.BENNETT			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ± 1 mm
X.X = ± 0.50 mm
X.XX = ± 0.10 mm
X.XXX = ± 0.01 mm
ANGLES = $\pm 5^\circ$
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²

TITLE: SMT SPRING CONTACT
(1.50mm HIGH)
IN TAPE AND REEL

DRAWING NUMBER:

S7251-45R

SHT
2 OF 2