



LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
AD	00		Z1	REVISED PER ECO-11-004917	11MAR11



- 1. REELED FOR MINI APPLICATOR.
- 2 PLATED WITH .00254 [.000100] TIN LEAD OVER .00127 [.000050] NICKEL ENTIRE CONTACT.
- 3 PLATED WITH .00076 [.000030] GOLD IN CONTACT AREA, GOLD FLASH ON REMAINDER, OVER .00127 [.000050] NICKEL.
- 4 SPRING MATERIAL: STAINLESS STEEL.
- 5 BODY MATERIAL: PHOSPHORUS BRONZE (SEE TABLE FOR FINISH.)
- 6 POINT OF PLATING MEASUREMENT.
- 7 INSULATION BARREL RANGE $\phi 0.71$ [.038]- $\phi 1.57$ [.062].
- 8 WIRE BARREL RANGE #20
- 9 PLATED WITH .00254 (.000100) TIN OVER .00127 (.000050) NICKEL, ENTIRE CONTACT.

SUPERSEDED BY 5-867052-1

9	5-867052-1
9	867052-3
3	867052-2
2	867052-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.BRANDBERG 17-1-93	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK S. SHUEY 26-1-93		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME CONTACT ASS'Y, LOCKING CLIP. FOR .025 SQUARE POST.	
0 PLC ± -		PRODUCT SPEC 108-36028		
1 PLC ± -		APPLICATION SPEC 114-25006	SIZE A2 CAGE CODE 00779 C=867052	
2 PLC ± -		WEIGHT -		
3 PLC ± 0.13 [.005]		CUSTOMER DRAWING	SCALE 10:1 SHEET 1 OF 1 REV Z1	
4 PLC ± -				
ANGLES ± -				
FINISH AS SHOWN				