BTA208S-600E

3Q Hi-Com Triac

Rev. 5 — 13 April 2011 Product data sheet

1. Product profile

1.1 General description

Planar passivated high commutation three quadrant triac in a surface-mountable plastic package. This "sries E" triac balances the requirements of commutation performance and gate sensitivity. The "sensitive gate" "series E" is intended for interfacing with low power drivers including microcontrollers.

1.2 Features and benefits

- 3Q technology for improved noise immunity
- Direct interfacing with low power drivers and microcontrollers
- Good immunity to false turn-on by dV/dt
- High commutation capability with sensitive gate
- High voltage capability
- Planar passivated for voltage ruggedness and reliability
- Surface-mountable package
- Triggering in three quadrants only

1.3 Applications

- Electronic thermostats
- General purpose motor controls

1.4 Quick reference data

Table 1. Quick reference data

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
V_{DRM}	repetitive peak off-state voltage		-	-	600	V
I_{TSM}	non-repetitive peak on-state current	full sine wave; $T_{j(init)}$ = 25 °C; t_p = 20 ms; see Figure 4; see Figure 5	-	-	65	A
$I_{T(RMS)}$	RMS on-state current	full sine wave; $T_{mb} \leq$ 102 °C; see Figure 1; see Figure 2; see Figure 3	-	-	8	A

Table 1. Quick reference data *...continued*

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Static characteristics						
I_{GT}	gate trigger current	V_D = 12 V; I_T = 0.1 A; T2+ G+; T_j = 25 °C; see Figure 7	-	-	10	mA
		V_D = 12 V; I_T = 0.1 A; T2+ G-; T_j = 25 °C; see Figure 7	-	-	10	mA
		V_D = 12 V; I_T = 0.1 A; T2- G-; T_j = 25 °C; see Figure 7	-	-	10	mA

2. Pinning information

Table 2. Pinning information

Pin	Symbol	Description	Simplified outline	Graphic symbol
1	T1	main terminal 1		
2	T2	main terminal 2		
3	G	gate		
mb	T2	mounting base; main terminal 2		



SOT428 (DPAK)



sym051

3. Ordering information

Table 3. Ordering information

Type number	Package		
	Name	Description	Version
BTA208S-600E	DPAK	plastic single-ended surface-mounted package (DPAK); 3 leads (one lead cropped)	SOT428

4. Limiting values

Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
V_{DRM}	repetitive peak off-state voltage		-	600	V
$I_{T(RMS)}$	RMS on-state current	full sine wave; $T_{mb} \leq 102$ °C; see Figure 1; see Figure 2; see Figure 3	-	8	A
I_{TSM}	non-repetitive peak on-state current	full sine wave; $T_{j(init)} = 25$ °C; $t_p = 20$ ms; see Figure 4; see Figure 5	-	65	A
		full sine wave; $T_{j(init)} = 25$ °C; $t_p = 16.7$ ms	-	72	A
I^2t	I^2t for fusing	$t_p = 10$ ms; sine-wave pulse	-	21	A^2s
dI_T/dt	rate of rise of on-state current	$I_T = 12$ A; $I_G = 0.2$ A; $dI_G/dt = 0.2$ A/µs	-	100	A/µs
I_{GM}	peak gate current		-	2	A
V_{GM}	peak gate voltage		-	5	V
P_{GM}	peak gate power		-	5	W
$P_{G(AV)}$	average gate power	over any 20 ms period	-	0.5	W
T_{stg}	storage temperature		-40	150	°C
T_j	junction temperature		-	125	°C



Fig 1. RMS on-state current as a function of heatsink temperature; maximum values



$f = 50$ Hz; $T_{mb} = 102$ °C

Fig 2. RMS on-state current as a function of surge duration; maximum value



α = conduction angle

Fig 3. Total power dissipation as a function of RMS on-state current; maximum values



f = 50 Hz

Fig 4. Non-repetitive peak on-state current as a function of the number of sinusoidal current cycles; maximum values



$t_p \leq 20\,\text{ms}$; (1) dI_T/dt limit

Fig 5. Non-repetitive peak on-state current as a function of pulse width; maximum values

5. Thermal characteristics

Table 5. Thermal characteristics

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
$R_{th(j\text{-}mb)}$	thermal resistance from junction to mounting base	full cycle; see Figure 6	-	-	2	K/W
		half cycle; see Figure 6	-	-	2.5	K/W
$R_{th(j\text{-}a)}$	thermal resistance from junction to ambient	in free air; printed circuit board (FR4) mounted	-	75	-	K/W



Fig 6. Transient thermal impedance from junction to mounting base as a function of pulse width

6. Characteristics

Table 6. Characteristics

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Static characteristics						
I_{GT}	gate trigger current	V_D = 12 V; I_T = 0.1 A; T2+ G+; T_j = 25 °C; see Figure 7	-	-	10	mA
		V_D = 12 V; I_T = 0.1 A; T2+ G-; T_j = 25 °C; see Figure 7	-	-	10	mA
		V_D = 12 V; I_T = 0.1 A; T2- G-; T_j = 25 °C; see Figure 7	-	-	10	mA
I_L	latching current	V_D = 12 V; I_G = 0.1 A; T2+ G+; T_j = 25 °C; see Figure 8	-	-	25	mA
		V_D = 12 V; I_G = 0.1 A; T2+ G-; T_j = 25 °C; see Figure 8	-	-	25	mA
		V_D = 12 V; I_G = 0.1 A; T2- G-; T_j = 25 °C; see Figure 8	-	-	30	mA
I_H	holding current	V_D = 12 V; T_j = 25 °C; see Figure 9	-	-	25	mA
V_T	on-state voltage	I_T = 10 A; T_j = 25 °C; see Figure 10	-	-	1.65	V
V_{GT}	gate trigger voltage	V_D = 12 V; I_T = 0.1 A; T_j = 25 °C; see Figure 11	-	-	1.5	V
		V_D = 400 V; I_T = 0.1 A; T_j = 125 °C; see Figure 11	0.25	-	-	V
I_D	off-state current	V_D = 600 V; T_j = 125 °C	-	-	0.5	mA
Dynamic characteristics						
dV_D/dt	rate of rise of off-state voltage	V_{DM} = 402 V; T_j = 110 °C; exponential waveform; gate open circuit	60	-	-	V/µs
dI_{com}/dt	rate of change of commutating current	V_D = 400 V; T_j = 125 °C; $I_{T(RMS)}$ = 8 A; dV_{com}/dt = 0.1 V/µs; gate open circuit	10	-	-	A/ms
		V_D = 400 V; T_j = 125 °C; $I_{T(RMS)}$ = 8 A; dV_{com}/dt = 10 V/µs; gate open circuit; see Figure 12	5	-	-	A/ms



(1) T2- G-

(2) T2+ G-

(3) T2+ G+

Fig 7. Normalized gate trigger current as a function of junction temperature



Fig 8. Normalized latching current as a function of junction temperature



Fig 9. Normalized holding current as a function of junction temperature



Vo = 1.264 V; Rs = 0.0378 Ω

(1) Tj = 125 °C; typical values

(2) Tj = 125 °C; maximum values

(3) Tj = 25 °C; maximum values

Fig 10. On-state current as a function of on-state voltage



Fig 11. Normalized gate trigger voltage as a function of junction temperature



Fig 12. Rate of change of commutating current as a function of junction temperature; minimum values

7. Package outline

Plastic single-ended surface-mounted package (DPAK); 3 leads (one lead cropped) **SOT428**



DIMENSIONS (mm are the original dimensions)

UNIT	A	A_1	b	b_1	b_2	c	D_1	D_2 min	E	E_1 min	e	e_1	H_D	L	L_1 min	L_2	w	y max
mm	2.38 2.22	0.93 0.46	0.89 0.71	1.1 0.9	5.46 5.00	0.56 0.20	6.22 5.98	4.0	6.73 6.47	4.45	2.285	4.57	10.4 9.6	2.95 2.55	0.5	0.9 0.5	0.2	0.2

OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	JEITA			
SOT428		TO-252	SC-63			~~06-02-14~~ 06-03-16

Fig 13. Package outline SOT428 (DPAK)

8. Revision history

Table 7. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
BTA208S-600E v.5	20110413	Product data sheet	-	BTA208S_SERIES_D_E_F_4
Modifications:	• The format of this data sheet has been redesigned to comply with the new identity guidelines of NXP Semiconductors. • Legal texts have been adapted to the new company name where appropriate. • Type number BTA208S-600E separated from data sheet BTA208S_SERIES_D_E_F_4.			
BTA208S_SERIES_D_E_F_4	20020301	Product specification	-	BTA208S_SERIES_D_E_F_3

9. Legal information

9.1 Data sheet status

Document status [1] [2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

9.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

9.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective

agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

9.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Adelante, **Bitport**, **Bitsound**, **CoolFlux**, **CoReUse**, **DESFire**, **EZ-HV**, **FabKey**, **GreenChip**, **HiPerSmart**, **HITAG**, **I²C-bus** logo, **ICODE**, **I-CODE**, **ITEC**, **Labelution**, **MIFARE**, **MIFARE Plus**, **MIFARE Ultralight**, **MoReUse**, **QLPAK**, **Silicon Tuner**, **SiliconMAX**, **SmartXA**, **STARplug**, **TOPFET**, **TrenchMOS**, **TriMedia** and **UCODE** — are trademarks of NXP B.V.

HD Radio and **HD Radio** logo — are trademarks of iBiquity Digital Corporation.

10. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

11. Contents

For more information, please visit: http://www.nxp.com
For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 13 April 2011
Document identifier: BTA208S-600E