

SMD Oscillators CMOS Output 5.0 x 3.2 x 0.75 mm TB Series

Oscillators
Series

Features


- Molded in plastic package
- Silicon-based MEMS oscillator
- Frequency range 1~150MHz
- High stability, low power consumption
- RoHS Compliant / Pb Free
- Main application : DSC, NB Computers, Computer Peripherals



Electrical Specifications


Item / Type	TB
Output Frequency Range	1~ 150MHz
Output Type	CMOS
Supply Voltage	1.8V, 2.5V, 3.3V
Frequency Stability	±25ppm
Operating Temperature Range	-40 ~ +85°C
Output Load	15pF Max.
Supply Current	25.0 mA Max.(1.0~ 60.0 MHZ Vdd=3.3V)
	30.0 mA Max. (60.0~ 133.33 MHZ Vdd=3.3V)
Voltage Vol (Max.) / Voh (Min.)	0.1 VDD / 0.9 VDD
Symmetry	45%~55% (1.0~ 100.0 MHz)
	40%~60% (100 ~ 200.0 MHz)
Rise / Fall Time	3 ns. Max.
Start-up Time	10msec Max.
Storage Temperature Range	-55 ~ +125°C

Dimensions



PAD FUNCTION:

- 1: OE / $\overline{ST}$
- 2: GND
- 3: OUT
- 4: VDD



Units: mm

Remark : Specification subject to change without prior notice. Please confirm with our sales.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TXC Corporation:

[TB-1.544MBD-T](#) [TB-1.544MCD-T](#) [TB-1.544MDD-T](#) [TB-1.8432MBD-T](#) [TB-1.8432MCD-T](#) [TB-1.8432MDD-T](#) [TB-10.000MBD-T](#) [TB-10.000MCD-T](#) [TB-10.000MDD-T](#) [TB-100.000MBD-T](#) [TB-100.000MCD-T](#) [TB-100.000MDD-T](#) [TB-106.250MBD-T](#) [TB-106.250MCD-T](#) [TB-11.0592MBD-T](#) [TB-11.0592MCD-T](#) [TB-11.0592MDD-T](#) [TB-12.000MBD-T](#) [TB-12.000MCD-T](#) [TB-12.000MDD-T](#) [TB-12.200MBD-T](#) [TB-12.200MCD-T](#) [TB-12.200MDD-T](#) [TB-12.288MBD-T](#) [TB-12.288MCD-T](#) [TB-12.288MDD-T](#) [TB-12.352MBD-T](#) [TB-12.352MCD-T](#) [TB-12.352MDD-T](#) [TB-12.500MBD-T](#) [TB-12.500MCD-T](#) [TB-12.500MDD-T](#) [TB-120.000MBD-T](#) [TB-120.000MCD-T](#) [TB-125.000MBD-T](#) [TB-125.000MCD-T](#) [TB-13.000MBD-T](#) [TB-13.000MCD-T](#) [TB-13.000MDD-T](#) [TB-13.513MBD-T](#) [TB-13.513MCD-T](#) [TB-13.513MDD-T](#) [TB-133.330MBD-T](#) [TB-133.330MCD-T](#) [TB-14.31818MBD-T](#) [TB-14.31818MCD-T](#) [TB-14.31818MDD-T](#) [TB-14.7456MBD-T](#) [TB-14.7456MCD-T](#) [TB-14.7456MDD-T](#) [TB-15.000MBD-T](#) [TB-15.000MCD-T](#) [TB-15.000MDD-T](#) [TB-15.8682MBD-T](#) [TB-15.8682MCD-T](#) [TB-15.8682MDD-T](#) [TB-150.000MBD-T](#) [TB-150.000MCD-T](#) [TB-16.000MBD-T](#) [TB-16.000MCD-T](#) [TB-16.000MDD-T](#) [TB-16.0972MBD-T](#) [TB-16.0972MCD-T](#) [TB-16.0972MDD-T](#) [TB-16.384MBD-T](#) [TB-16.384MCD-T](#) [TB-16.384MDD-T](#) [TB-18.432MBD-T](#) [TB-18.432MCD-T](#) [TB-18.432MDD-T](#) [TB-19.200MBD-T](#) [TB-19.200MCD-T](#) [TB-19.200MDD-T](#) [TB-19.440MBD-T](#) [TB-19.440MCD-T](#) [TB-19.440MDD-T](#) [TB-20.000MBD-T](#) [TB-20.000MCD-T](#) [TB-20.000MDD-T](#) [TB-22.1184MBD-T](#) [TB-22.1184MCD-T](#) [TB-22.1184MDD-T](#) [TB-22.5792MBD-T](#) [TB-22.5792MCD-T](#) [TB-22.5792MDD-T](#) [TB-24.000MBD-T](#) [TB-24.000MCD-T](#) [TB-24.000MDD-T](#) [TB-24.576MBD-T](#) [TB-24.576MCD-T](#) [TB-24.576MDD-T](#) [TB-25.000625MBD-T](#) [TB-25.000625MCD-T](#) [TB-25.000625MDD-T](#) [TB-25.000MBD-T](#) [TB-25.000MCD-T](#) [TB-25.000MDD-T](#) [TB-26.000MBD-T](#) [TB-26.000MCD-T](#) [TB-26.000MDD-T](#)