


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

CODE	DIM "M" MATING LENGTH	CONTACT TYPE
E	[N/A]	SIGNAL
PA	[1.07]	POWER

PRODUCT NO.	ROWS	POWER				SIGNAL				POWER						
		E2	P9	P8	P7	4	3	2	1	P6	P5	P4	P3	P2	P1	E1
51940-157-- NOTE: 3	D C B A															



mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date					COPY		www.fciconnect.com	
A	DG05-0246	SW	07/26/05	linear		0.X ± 0.5		projection		title	
B	DG05-0271	SW	08/09/05			0.XX ± 0.25				6P + 16S + 3ACP	
C	DG09-0093	JW	04/07/09	angles		0.XXX ± 0.13				VERTICAL STB RECEPT	
						0° + 2°		scale		product family	PwrBlade
				dr	STEVEN WANG	07/26/05				size	code
				enrg	M. MOSTOLLER	mm/dd/yy				dwg no	213
				chr	VICTOR LIN	07/26/05				51940-157	
				appd	JOSEPH HSIA	07/26/05				sheet	1 of 4
sheet index	revision sheet	C	C	C	C						
		1	2	3	4						




cage code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51940-157--
NOTE: 3



mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
litr	ecn no.	dr	date	linear			0.X ± 0.5	projection	COPY	title	product family	code	size
C							0.XX ± 0.25						
							0.XXX ± 0.13						
				angles			0° ± 2°	MIM	scale	A	PwrBlade	213	sheet 2
				dr	STEVEN WANG	07/26/05							
				enrg	M. MOSTOLLER	mm/dd/yy							
				chr	VICTOR LIN	07/26/05		1:1	A	51940-157	cage code	22526	4
				appd	JOSEPH HSIA	07/26/05							
sheet index	revision sheet												


Pro/E

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51940-157_-
NOTE: 3



mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	0.X ± 0.5	COPY		www.fciconnect.com	
C				linear	0.XX ± 0.25	projection		title	
				angles	0.XXX ± 0.13			6P + 16S + 3ACP	
				dr	0° ± 2°			VERTICAL STB RECEPT	
				enr	STEVEN WANG 07/26/05	MIM		product family	PwrBlade
				chr	M. MOSTOLLER mm/dd/yy	scale		size	213
				appd	VICTOR LIN 07/26/05	1:1		dwg no	3
					JOSEPH HSIA 07/26/05			51940-157	
sheet index	revision sheet								

cage code
22526

Pro/E

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER	
51940-157_- NOTE: 3	
NOTES:	
1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.	
CONNECTOR NOTES:	
2 HOUSING MATERIAL: UL 94 V-0 GLASS FILLED HIGH-TEMP THERMOPLASTIC POWER CONTACT MATERIAL: COPPER ALLOY SIGNAL PIN MATERIAL: COPPER ALLOY	
3. PLATING: SEE ITEM 5 & 6 IN PRINT 10064183 FOR PLATING SPEC OF 51940-157, 51940-157LF RESPECTIVELY.	
4 MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.	
5. PRODUCT SPECIFICATION GS-12-149. APPLICATION SPECIFICATION BUS-20-067.	
6. PACKAGED IN TRAYS.	
PCB NOTES:	
7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.	
8 MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.	
9 $\varnothing 1.151 \pm 0.025$ DRILLED HOLES PLATED WITH 0.008 MIN SnPb OVER 0.03 TO 0.08 Cu PLATING TO ACHIEVE $\varnothing 1.02 \pm .07$ HOLE.	
10 "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.	
11 CONNECTOR KEEP-OUT ZONE.	
12. A Δ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.	

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com	
litr	ecn no.	dr	date	linear	0.X $\pm$ 0.5			COPY		title 6P + 16S + 3ACP VERTICAL STB RECEPT	
C					0.XX $\pm$ 0.25			projection			
					0.XXX $\pm$ 0.13						
				angles	0° $\pm$ 2°					product family PwrBlade code 213	
				dr	STEVEN WANG	07/26/05	MIM				
				enrg	M. MOSTOLLER	mm/dd/yy					
				chr	VICTOR LIN	07/26/05	scale		size A		dwg no 51940-157 sheet 4
				appd	JOSEPH HSIA	07/26/05	1:1		cage code 22526		
sheet index		revision sheet									