

Customer Specification

PART NO. 9316

Construction

				Diameters (In)	
1) Component 1		1 X 1 COND			
a) Conductor		25 (7/.0067) AWG SCW		0.020	
b) Insulation		0.020" Wall, Nom. PTFE		0.060	
(1) Color(s)					
Cond	Color	Cond	Color	Cond	Color
1	CLEAR				
2) Shield		SPC BRAID Shield,94% Coverage, Min.			
3) Jacket		0.010" Wall, Nom.,FEP		0.098 (0.102 Max.)	
a) Color(s)		NATURAL TAN			
b) Print		ALPHA WIRE-* P/N 9316 MIL-DTL-17 M17/113-RG 316 12814 E346462 1C 26 AWG SHIELDED 200C (UL) C(UL) CMG FT4 OR AWM 1971 150C 125V ROHS * = Factory Code [Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]			

Applicable Specifications

1) UL	AWM/STYLE 1971	150°C / 125 V _{RMS}
	CMG	200°C
2) CSA International	C(UL) TYPE CMG	200°C
	FT4	
3) Military	MIL-C-17/113 RG 316/U	200°C / 900 V _{RMS}

Environmental

1) EU Directive 2002/95/EC(RoHS):	
	All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.
2) California Proposition 65:	The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

Properties

Physical & Mechanical Properties	
1) Temperature Range	-55 to 200°C
2) Bend Radius	10X Cable Diameter
3) Pull Tension	2.11 Lbs, Maximum
Electrical Properties	(For Engineering purposes only)
1) Voltage Rating	900 V _{RMS}
2) Characteristic Impedance	50 +/- 2
3) Ground Capacitance	29.3 pf/ft @1 kHz, Nominal
4) Velocity of Propagation	70 %
5) Conductor DCR	85.8 /1000ft @20°C, Nominal
6) OA Shield DCR	8.5 /1000ft @20°C, Nominal
7) Voltage Withstanding	2 kV, Minimum
8) Corona Extinction	1.2 kV, Minimum
9) SRL, db Minimum	30 @ 50 Mhz
	30 @ 100 MHz
	23 @ 400 MHz
	21 @ 1 GHz
	17 @ 3 GHz
10) Attenuation, Max dB/100ft	7.5 @ 50 MHz
	11 @ 100 MHz
	21 @ 400 MHz
	38 @ 1 GHz
	58 @ 3 GHz

Other

Packaging	Flange x Traverse x Barrel (inches)
a) 1000 FT	9 x 4.5 x 3.5 Max. 3 separate pieces; Min length/piece 100 FT.
b) 500 FT	6.5 x 4 x 2.5 Max. 2 separate pieces; Min length/piece 100 FT.
c) 100 FT	3.5 x 3 x 1.125 Continuous length
d) Bulk(Made-to-order)	(Max 3 peices per 1000 Ft/ Min length 100ft)
	<i>[Spool dimensions may vary slightly]</i>

www.alphawire.com

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207
Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha Wire:](#)

[9316 BR002](#)