

HIGH FREQUENCY MAGNETICS

T1/E1 Single Through Hole Transformers

TM00155


- Operate over DS1 rates (1.544 Mbits/s) and CEPT international rates (2.048 Mbits/s)
- Service the transmit side of the line interface
- Only difference between 2662K and 2662K2 is the terminal length
- Inductance unbalance of center-tapped winding is 0.3%, max
- Recommended transformer for new through-hole applications is 2745CA2
- Operating Temperature Range: -40° to +85° C
- Meets IEC 695, 2-2 flammability requirements
- PWB Process Capability: Standard Printed Wiring Board assembly techniques, total-immersion cleaning
- Reliability testing: Shock, vibration, temperature cycling, temperature - humidity - bias

ELECTRICAL SPECIFICATIONS AT 25° C

Part Number	Turns Ratio ± 2%	Inductance μH min ¹	DCR Ω max		Leakage Inductance ² μH max	Effective Distributed Capacitance pF	Primary ET Constant V-μs	Minimum Interwinding Breakdown Voltage Vrms
	(1-3):(4-6)	(1-3)	(1-3)	(4-6)				
2662K	1 : 1.37 CT	680	1.0	1.4	1.3	15	21	500
2662K2	1 : 1.37 CT	680	1.0	1.4	1.3	15	21	500

1. measured at 10 kHz, 0.1 Vac
2. measured at 100 kHz, 0.1 Vac


SCHEMATIC



HIGH FREQUENCY MAGNETICS

T1/E1 Single Through Hole Transformers

MECHANICAL



Unless otherwise specified, dimensions are nominal and in inches (millimeters).

©2000 Bel Fuse Inc. Specifications subject to change without notice. 08.00

CORPORATE

Bel Fuse Inc.
198 Van Vorst Street
Jersey City, NJ 07302
Tel 201-432-0463
Fax 201-432-9542
www.belfuse.com

FAR EAST

Bel Fuse Ltd.
8F / 8 Luk Hop Street
San Po Kong
Kowloon, Hong Kong
Tel 852-2328-5515
Fax 852-2352-3706
www.belfuse.com

EUROPE

Bel Fuse Europe Ltd.
Preston Technology Management Centre
Marsh Lane, Suite G7, Preston
Lancashire, PR1 8UD, U.K.
Tel 44-1772-556601
Fax 44-1772-888366
www.belfuse.com